




Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For treated water (application range according to Technical Information „Treated water“)
- For rainwater with a pH value ≥ 5.5
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)

CHARACTERISTICS

- Approval in accordance with DVGW
- Model Geberit K4
- Ball and base unit fully exposed to flow
- Replaceable valve top with ball and seals
- With concealed turn handle
- Base unit made of stainless steel
- Upper part made of gunmetal
- Ball made of PPSU
- Upper part caulk made of EPDM
- Ball caulks made of silicone
- Pressing indicator
- Leaky if unpressed

- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating temperature	0–95 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

SCOPE OF DELIVERY

- Concealed turn handle
- Spindle extension
- Round protection box, can be shortened
- Protection cover plug with marking tip

Art. no.	DNV	DN	d, ø mm	L cm	L1 cm	Z cm	K cm	PN bar
94912	15	12	15	10.4	12.6	3.2	7.3	10
94913	15	15	18	10.3	12.6	3.2	7.3	10

Art. no.	DNV	DN	d _ø mm	L cm	L1 cm	z cm	K cm	PN bar
94914	20	20	22	11.7	12.6	3.8	7.3	10