



-1. Torque tools

-1.1. TORQUE TOOLS

- Digital torque tester
- 2 Installation options, on a wall or fastened in a vice
- LCD touch pad screen, coloured graphic display
- Downloads stored torque data to a PC
- Units of torque: Nm, kgcm, ft.lb., in.lb., in-oz
- Audible (tone) and LED light-bar
- Present alerts torque accuracy: $\pm 0.5\%$ ± 1 count CW and CCW from 10 to 100% of full scale at 25° C
- Display accuracy: 4 digits, 9999 cycle counts
- Six "AA" Alkaline cells for battery power included
- Track, peak and first peak modes of operation
- Operating temperature: 40 to 110° F (5 to 42° C)
- Storage temperature: 0 to 122° F (-20 to 50° C); Humidity up to 85% non-condensing
- Manual available in 9 languages
- Traceability from 10% to 100% of full scale. Includes storage case, AC adapter and USB cable
- ISO-6789-2003 and ASME B107-28-2005 standards compliant

Torque Control

DTT



69DTT-5	7314150184132	1	1/4"	0,5-5	0,4-4	4,4-44	5.000
74DTT-100	7314150184149	1	3/8"	10-100	7-75	88-880	5.000
78DTT-340	7314150182626	1	1/2"	34-340	25-250	300-3.000	5.000
89DTT-800	7314150184156	1	3/4"	80-800	60-580	705-7.050	5.000