


Geberit Mapress Stainless Steel adaptor with union nut (silicone-free)



Example image

APPLICATION PURPOSES

- For cold and hot potable water
 - For cooling and heating water without antifreeze agent
 - For cooling and heating water with antifreeze agent
 - For district heating water ≤ 120 °C
 - For saturated steam ≤ 120 °C
 - For service water and process water
 - For treated water
 - For grey and black water with a pH value ≥ 5.5
 - For extinguishing water (wet)
 - For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
 - For chemicals and technical liquids
 - For compressed air (oil purity class 0–3)
 - For negative pressure
 - For inert gases (e.g. nitrogen)
 - For industrial gases (e.g. acetylene, shielding gases)
 - Suitable exclusively for threads with an inner diameter of ≤ di, see table
 - For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Union nut made of brass
- Seal ring made of CIIR, black
- Flat gasket made of EPDM

TECHNICAL DATA

Medium temperature with flat gasket EPDM	0–100 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	G	di, ø mm	L cm	Z cm
85042	12	15	1/2	10	5.1	2.5
85032	12	15	3/4	13	3.7	1.1
85072	12	15	1 1/4	26	4.3	1.3

Art. no.	DN	d, ø mm	G "	di, ø mm	L cm	Z cm
85033	15	18	3/4	13	3.7	1.1
85034	20	22	1	20	4	1.1
85044	20	22	1 1/4	26	4.3	1.3
85045	20	22	1 1/2	32	4.4	1.3
85046	25	28	1	20	5.5	2.4
85035	25	28	1 1/4	26	4.4	1.3
85047	25	28	1 1/2	32	4.6	1.3
85036	32	35	1 1/2	32	4.8	1.3
85037	40	42	1 3/4	39	5.2	1.3
85038	50	54	2 3/8	51	5.8	1.5