



SAFETY DATA SHEET

Whiteboard Cleaner 250ml Pump Spray

According to Regulation (EC) No 1907/2006, Annex II, as amended.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Whiteboard Cleaner 250ml Pump Spray

Product number ABCL250, ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier

AF INTERNATIONAL. A division of HK WENTWORTH LTD
 ASHBY PARK
 COALFIELD WAY
 ASHBY de la ZOUCH
 LEICESTERSHIRE. LE65 1JR
 UNITED KINGDOM
 +44 (0) 1530 419600
 +44 (0) 1530 416640
 info@hkw.co.uk

1.4. Emergency telephone number

Emergency telephone +44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

2.2. Label elements

Hazard statements EUH208 Contains 1,2-Benzisothiazol-3(2H)-one, Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

Precautionary statements P102 Keep out of reach of children.

Detergent labelling < 5% non-ionic surfactants, Contains BENZISOTHIAZOLINONE, METHYLISOTHIAZOLINONE, METHYLCHLOROISOTHIAZOLINONE AND METHYLISOTHIAZOLINONE

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

Whiteboard Cleaner 250ml Pump Spray

SECTION 3: Composition/information on ingredients

3.2. Mixtures

1-Methoxy-2-propanol		10-30%
CAS number: 107-98-2	EC number: 203-539-1	REACH registration number: 01-2119457435-35-XXXX
Classification		
Flam. Liq. 3 - H226		
STOT SE 3 - H336		

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel.
Inhalation	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if any discomfort continues.
Ingestion	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Rinse mouth. Get medical attention if any discomfort continues.
Skin contact	No specific recommendations. Rinse with water. Get medical attention if any discomfort continues.
Eye contact	Rinse with water. Get medical attention if any discomfort continues.
Protection of first aiders	Use protective equipment appropriate for surrounding materials.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known. Spray/mists may cause respiratory tract irritation.
Ingestion	No specific symptoms known. May cause discomfort if swallowed.
Skin contact	No specific symptoms known. May cause discomfort.
Eye contact	No specific symptoms known. May be slightly irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
Specific treatments	No special treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Whiteboard Cleaner 250ml Pump Spray

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.
5.3. Advice for firefighters	
Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions No specific recommendations. For personal protection, see Section 8.

6.2. Environmental precautions

Environmental precautions Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Reuse or recycle products wherever possible. Absorb spillage to prevent material damage. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Avoid discharge to the aquatic environment.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions No specific recommendations.

Storage class Unspecified storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

1-Methoxy-2-propanol

Whiteboard Cleaner 250ml Pump Spray

Long-term exposure limit (8-hour TWA): WEL 100 ppm 375 mg/m³

Short-term exposure limit (15-minute): WEL 150 ppm 560 mg/m³

Sk

Ethanol

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1920 mg/m³

WEL = Workplace Exposure Limit

Sk = Can be absorbed through the skin.

8.2. Exposure controls

Appropriate engineering controls	No specific ventilation requirements.
Eye/face protection	No specific eye protection required during normal use. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.
Hand protection	No specific hand protection recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Not regarded as dangerous for the environment.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	Characteristic.
Odour threshold	Not available.
pH	pH (concentrated solution): 6.5-9
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	Not available.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.

Whiteboard Cleaner 250ml Pump Spray

Relative density	Not available.
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects Not regarded as a health hazard under current legislation.

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Whiteboard Cleaner 250ml Pump Spray

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

Contains a substance/a group of substances which may cause cancer. IARC Group 1
Carcinogenic to humans.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

No specific symptoms known. Spray/mists may cause respiratory tract irritation.

Ingestion

No specific symptoms known. May cause discomfort if swallowed.

Skin contact

No specific symptoms known. May cause discomfort.

Eye contact

No specific symptoms known. May be slightly irritating to eyes.

Route of entry

Ingestion Inhalation Skin and/or eye contact

Target organs

No specific target organs known.

1-Methoxy-2-propanol

Acute toxicity - oral

**Acute toxicity oral (LD₅₀
mg/kg)** 3,739.0

Species Rat

Notes (oral LD₅₀) LD₅₀ 3739 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

ATE oral (mg/kg) 3,739.0

Whiteboard Cleaner 250ml Pump Spray

Acute toxicity - dermal

Notes (dermal LD₅₀)

LD₅₀ >2000 mg/kg, Dermal, Rat REACH dossier information. Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data

Dose: 0.5 mL, 4 hours, Rabbit Erythema/eschar score: No erythema (0). Oedema score: No oedema (0). REACH dossier information. Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation

Guinea pig maximization test (GPMT) - Guinea pig: Not sensitising. REACH dossier information. Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro

Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Genotoxicity - in vivo

Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity

NOEL 3000 ppm, Inhalation, Mouse REACH dossier information. Based on available data the classification criteria are not met.

Reproductive toxicity

Reproductive toxicity - fertility

Two-generation study - NOEL 1000 ppm, Inhalation, Rat F1 REACH dossier information. Based on available data the classification criteria are not met.

Reproductive toxicity - development

Teratogenicity: - NOEL: 1500 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure

STOT SE 3 - H336 May cause drowsiness or dizziness. REACH dossier information.

Target organs

Central nervous system Brain

Specific target organ toxicity - repeated exposure

STOT - repeated exposure

NOAEL 919 mg/kg/day, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

2-Methoxypropanol

Acute toxicity - oral

Notes (oral LD₅₀)

LD₅₀ 5710 mg/kg, Oral, Rat Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀)

LD₅₀ 5660 mg/kg, Dermal, Rabbit Based on available data the classification criteria are not met.

Skin corrosion/irritation

Skin corrosion/irritation

Irritating to skin.

Serious eye damage/irritation

Whiteboard Cleaner 250ml Pump Spray

Serious eye damage/irritation May cause serious eye damage.

Reproductive toxicity

Reproductive toxicity - development Maternal toxicity: - Dose level:: 545 ppm, Inhalation, Rabbit May damage the unborn child.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H335 May cause respiratory system irritation.

Target organs Respiratory system, lungs

Ethanol

Toxicological effects Not regarded as a health hazard under current legislation.

Acute toxicity - oral

Notes (oral LD₅₀) LD₅₀ 10470 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) LD₅₀ 124.7 mg/l, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Dose: 0.2 mL, 24 hours, Rabbit Primary dermal irritation index: 0 REACH dossier information. Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Local Lymph Node Assay (LLNA) - Mouse: Not sensitising. REACH dossier information. Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Genotoxicity - in vivo Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Carcinogenicity

IARC carcinogenicity IARC Group 1 Carcinogenic to humans.

Reproductive toxicity

Reproductive toxicity - fertility Two-generation study - NOAEL 15% , Oral, Mouse REACH dossier information. Based on available data the classification criteria are not met.

Reproductive toxicity - development Maternal toxicity: - NOAEL: 16000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure LOAEL ~4000 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

SECTION 12: Ecological Information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

Whiteboard Cleaner 250ml Pump Spray

12.1. Toxicity

Toxicity

Based on available data the classification criteria are not met.

1-Methoxy-2-propanol

Acute toxicity - fish	LC ₅₀ , 96 hours: 20800 mg/l, Pimephales promelas (Fat-head Minnow) REACH dossier information.
Acute toxicity - aquatic invertebrates	LC ₅₀ , 48 hours: 21100 mg/l, Daphnia magna REACH dossier information.
Acute toxicity - aquatic plants	EC ₅₀ , 7 days: >1000 mg/l, Selenastrum capricornutum REACH dossier information.

2-Methoxypropanol

Acute toxicity - fish	LC ₅₀ , 96 hours: >1006 mg/l, Algae, Estimated value.
Acute toxicity - aquatic invertebrates	EC ₅₀ , 48 hours: >13205 mg/l, Daphnia magna, Estimated value.

Ethanol

Toxicity	Based on available data the classification criteria are not met.
Acute toxicity - fish	LC ₅₀ , 96 hours: 14200 mg/l, Pimephales promelas (Fat-head Minnow)
Acute toxicity - aquatic invertebrates	LC ₅₀ , 48 hours: 5012 mg/l, Ceriodaphnia dubia
Acute toxicity - aquatic plants	EC ₅₀ , 72 hours: 11.5 mg/l, Chlorella vulgaris
Chronic toxicity - aquatic invertebrates	NOEC, 9 days: 9.6 mg/l, Daphnia magna

12.2. Persistence and degradability

Persistence and degradability The degradability of the product is not known.

1-Methoxy-2-propanol

Persistence and degradability	The substance is readily biodegradable.
Phototransformation	Water - DT ₅₀ : 3.1 hours REACH dossier information.
Biodegradation	Water - Degradation 96%: 28 days REACH dossier information.

2-Methoxypropanol

Biodegradation	No data available.
-----------------------	--------------------

Ethanol

Whiteboard Cleaner 250ml Pump Spray

Persistence and degradability	The substance is readily biodegradable.
Biodegradation	Water - Degradation 74%: 10 days
Chemical oxygen demand	1.99 g O ₂ /g substance

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
Partition coefficient	Not available.

1-Methoxy-2-propanol

Bioaccumulative potential	No data available on bioaccumulation.
Partition coefficient	log Pow: <1 REACH dossier information.

2-Methoxypropanol

Bioaccumulative potential	BCF: ~ 1 - 10, Estimated value. Bioaccumulation is unlikely.
----------------------------------	--

Ethanol

Bioaccumulative potential	Bioaccumulation is unlikely.
Partition coefficient	log Pow: -0.35

12.4. Mobility in soil

Mobility	No data available.
-----------------	--------------------

1-Methoxy-2-propanol

Mobility	Mobile.
Surface tension	70.7 mN/m @ 20°C

2-Methoxypropanol

Mobility	Soluble in water.
Adsorption/desorption coefficient	- log Kow: ~ (-0.45) - (-0.49) @ 25°C Calculation method. - Log Koc: ~ 0.0 - 1.13 @ 25°C Calculation method.

Ethanol

Mobility	The product is soluble in water.
Surface tension	24.5 mN/m @ 20°C/68°F

12.5. Results of PBT and vPvB assessment

1-Methoxy-2-propanol

Results of PBT and vPvB assessment	This substance is not classified as PBT or vPvB according to current EU criteria.
---	---

2-Methoxypropanol

Whiteboard Cleaner 250ml Pump Spray

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current EU criteria.

Ethanol

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current EU criteria.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78 and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Whiteboard Cleaner 250ml Pump Spray

National regulations	Health and Safety at Work etc. Act 1974 (as amended). The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.
EU legislation	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 453/2010 of 20 May 2010. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). Dangerous Preparations Directive 1999/45/EC. Dangerous Substances Directive 67/548/EEC.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Training advice	Read and follow manufacturer's recommendations.
Issued by	Toni Ashford
Revision date	24/05/2016
Revision	1
SDS number	188
Hazard statements in full	H225 Highly flammable liquid and vapour. H226 Flammable liquid and vapour. H336 May cause drowsiness or dizziness. EUH208 Contains 1,2-Benzisothiazol-3(2H)-one, Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.