

#### 400W SURFACE MOUNT AUTOMOTIVE TRANSIENT VOLTAGE SUPPRESSOR

### Product Summary (@TA = +25°C)

PPK	IFSM	V <sub>RWM</sub>	PM <sub>(AV)</sub>	
400W	40A	5V to 200V	5W	

## **Description and Applications**

Suitable to protect sensitive automotive circuits against surges defined in ISO7637-2 and against electrostatic discharges according to ISO10605.

Compliance with following standards

- ISO10605, C = 150pF, R = 330Ω: 30kV (Air Discharge)
   30kV (Contact Discharge)
  - ISO7637-2 (Note 5)
    Pulse 1: Vs = -100V
    Pulse 2a: Vs = +50V
    Pulse 3a: Vs = -150V
    Pulse 3b: Vs = +100V

## **Features and Benefits**

- 400W Peak Pulse Power Dissipation
- 5V to 200V Standoff Voltages
- Glass Passivated Die Construction
- Unidirectional and Bidirectional Versions Available
- Excellent Clamping Capability
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The SMAJ5.0(C)AQ SMAJ200(C)AQ is suitable for automotive applications requiring specific change control; these parts are AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

#### **Mechanical Data**

- Case: SMA
- Case Material: Molded Plastic.
  - UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead-Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208(3)
- Polarity Indicator: Cathode Band (Bidirectional Devices do not have a Polarity Indicator)
- Weight: 0.064 grams (Approximate)

#### **SMA**







Bottom View

### **Ordering Information (Note 4)**

Part Number	Qualification	Case	Packaging
SMAJX.X(C)AQ-13-F	Automotive	SMA	5000/Tape & Reel
SMAJXX(C)AQ-13-F	Automotive	SMA	5000/Tape & Reel
SMAJXXX(C)AQ-13-F	Automotive	SMA	5000/Tape & Reel

<sup>\*</sup>X = Device Voltage, Example: SMAJ14AQ-13-F

Notes: 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
- 5. Not applicable to parts with stand-off voltage lower than the average battery voltage (13.5V).

# **Marking Information**



xx = Product Type Marking Code
(See Electrical Characteristics Table)

J!! = Manufacturers' Marking

YWW = Date Code Marking

Y = Last Digit of Year (ex: 0 for 2020)

WW = Week Code (01 to 53)



## **Maximum Ratings** (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Peak Pulse Power Dissipation	РРК	400	W	
(Non-Repetitive Current Pulse Derated Above T <sub>A</sub> = +25°C) (Note 6)			VV	
Peak Forward Surge Current, 8.3ms Single Half Sine Wave	Irou	40	Δ	
Superimposed on Rated Load (Notes 6, 7 & 8)	IFSM	40	A	
Steady State Power Dissipation @ T <sub>L</sub> = +75°C	PM <sub>(AV)</sub>	1.0	W	
Instantaneous Forward Voltage @ IPP = 35A (Notes 6, 7 & 8)	VF	3.5	V	

Notes:

- 6. Valid provided that terminals are kept at ambient temperature.
- 7. Measured with 8.3ms single half sine-wave. Duty cycle = 4 pulses per minute maximum.
- 8. Unidirectional units only.

## **Thermal Characteristics**


Characteristic	Symbol	Value	Unit
Operating Temperature Range	TJ	-55 to +150	°C
Storage Temperature Range	T <sub>STG</sub>	-55 to +175	°C

# **Electrical Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Part Number Add C For Bidirectional (Note 9)	Reverse Standoff Voltage	Volt V <sub>BR</sub>	kdown tage @ I <sub>T</sub> e 10)	Test Current	Max. Reverse Leakage @ V <sub>RWM</sub> (Note 12)	Max. Clamping Voltage @ IPP (Note 11)	Max. Peak Pulse Current	Markin	g Code
(Note 9)	VRWM (V)	Min (V)	Max (V)	IT (mA)	I <sub>R</sub> (μA)	Vc (V)	IPP (A)	BI-	UNI-
SMAJ5.0(C)AQ	5.0	6.40	7.25	10	800	9.2	43.5	TE	HE
SMAJ8.5(C)AQ	8.5	9.44	10.4	1.0	10	14.4	27.7	TT	HT
SMAJ12(C)AQ	12	13.3	14.7	1.0	5.0	19.9	20.1	UE	IE
SMAJ13(C)AQ	13	14.4	15.9	1.0	5.0	21.5	18.6	UG	IG
SMAJ14(C)AQ	14	15.6	17.2	1.0	5.0	23.2	17.2	UK	IK
SMAJ15(C)AQ	15	16.7	18.5	1.0	5.0	24.4	16.4	UM	IM
SMAJ16(C)AQ	16	17.8	19.7	1.0	5.0	26.0	15.3	UP	IP
SMAJ17(C)AQ	17	18.9	20.9	1.0	5.0	27.6	14.5	UR	IR
SMAJ18(C)AQ	18	20.0	22.1	1.0	5.0	29.2	13.7	UT	IT
SMAJ20(C)AQ	20	22.2	24.5	1.0	5.0	32.4	12.3	UV	IV
SMAJ22(C)AQ	22	24.4	26.9	1.0	5.0	35.5	11.2	UX	IX
SMAJ24(C)AQ	24	26.7	29.5	1.0	5.0	38.9	10.3	UZ	ΙZ
SMAJ26(C)AQ	26	28.9	31.9	1.0	5.0	42.1	9.5	VE	JE
SMAJ28(C)AQ	28	31.1	34.4	1.0	5.0	45.4	8.8	VG	JG
SMAJ30(C)AQ	30	33.3	36.8	1.0	5.0	48.4	8.3	VK	JK
SMAJ33(C)AQ	33	36.7	40.6	1.0	5.0	53.3	7.5	VM	JM
SMAJ36(C)AQ	36	40.0	44.2	1.0	5.0	58.1	6.9	VP	JP
SMAJ40(C)AQ	40	44.4	49.1	1.0	5.0	64.5	6.2	VR	JR
SMAJ43(C)AQ	43	47.8	52.8	1.0	5.0	69.4	5.7	VT	JT
SMAJ51(C)AQ	51	56.7	62.7	1.0	5.0	82.4	4.9	VZ	JZ
SMAJ58(C)AQ	58	64.4	71.2	1.0	5.0	93.6	4.3	WG	RG
SMAJ60(C)AQ	60	66.7	73.7	1.0	5.0	96.8	4.1	WK	RK
SMAJ70(C)AQ	70	77.8	86.0	1.0	5.0	113	3.5	WP	RP
SMAJ78(C)AQ	78	86.7	95.8	1.0	5.0	126	3.2	WT	RT
SMAJ170(C)AQ	170	189	209	1.0	5.0	275	1.4	XR	SR
SMAJ200(C)AQ	200	224	248	1.0	1.0	324	1.2	YT	ST


Notes:

- 9. Suffix C denotes bidirectional device.
- 10.  $V_{BR}$  measured with  $I_T$  current pulse = 10ms to 15ms.
- 11. Per  $10 \times 1000 \mu s$  waveform. See Figure 4.
- 12. For bidirectional devices having  $V_{\text{RWM}}$  of 10V and under, the  $I_{\text{R}}$  is doubled.












Fig. 5 Maximum Non-Repetitive Surge Current





Fig. 2 Typical Total Capacitance



t, TIME (ms) Fig. 4 Pulse Waveform





Fig. 6 Steady State Power Derating Curve



## **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### SMA




SMA					
Dim	Min	Max			
Α	2.29	2.92			
В	4.00	4.60			
С	1.27	1.63			
D	0.15	0.31			
Е	4.80	5.59			
G	0.05	0.20			
Н	0.76	1.52			
J	1.96	2.40			
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### SMA



Dimensions	Value		
פווטופווסוטווס	(in mm)		
С	4.00		
G	1.50		
Х	2.50		
X1	6.50		
Υ	1 70		





#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### **LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com