

Parker Product Datasheet



Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

PART NUMBER: 1010T04A01

COLOR: BLACK

LENGTH (M): 10

TUBE I.D. (MM): 2

TUBING MATERIAL: ANTISTATIC PFA TUBING

TUBE O.D. (MM): 4

PRODUCT OVERVIEW

Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

Features/Benefits:

- Great Versatility

- Exceptional chemical inertia

- A flexible alternative to stainless steel tubing
- Broad range of working temperatures, from cryogenic to extreme heat
- Non-stick properties allowing conveyance of many fluids & gases
- Outstanding resistance to ageing
- Fluoropolymer with the lowest permeability
- Non-flammable
- UV-transparent
- Tube marking on request
- Silicone-free

- Three Material Grades

- Clear PFA: to cover all applications, including those requiring maximum mechanical resistance
- Colored PFA: for circuit identification
- Black Antistatic PFA: eliminates all risk of electrostatic discharge

Markets:

- Food and Beverage
- Power Generation Equipment
- Aircraft
- Pharmaceutical
- Medical
- Oil and Gas

Applications:

- Applications Subjected to Severe Mechanical and Chemical Conditions
- Medical Fluids Conveying
- Gas and Compressed Air Conveying
- Applications Requiring Very Low and High Temperature
- Fire Hazard Zones
- Applications Subjected to Intensive Cleaning
- Suitable for Fuel Cells and Clean Rooms
- Thermal Management

Technologies:

- Fluoropolymer Tubing
- PFA Tubing
- Perfluoro alkoxy Tubing
- Anti Static Tubing
- Industrial Tubing

TECH SPECIFICATIONS

**MAXIMUM OPERATING
TEMPERATURE**

150 °C

DIVISION

Low Pressure Connectors Europe Division

MAXIMUM OPERATING PRESSURE 33 bar

MINIMUM OPERATING TEMPERATURE	-40 °C
SPECIFICATIONS MET	RoHS 2002/95/EC, 2011/65/EC (Industrial)
SPECIFICATIONS MET	PED 97/23/EC (Industrial)
SPECIFICATIONS MET	REACH 1907/2006 (Industrial)
SPECIFICATIONS MET	ATEX 94/9/EC (black tubing, industrial)
SPECIFICATIONS MET	FDA 21 CFR 177.1550 (clear)
SPECIFICATIONS MET	USP Class VI (A). Medical: External Communication Devices
SPECIFICATIONS MET	UL 94 V-0 (Fire Resistance, Industrial)
MEDIA	Medical Fluids
MEDIA	Food & Beverage
MEDIA	Industrial Gases
MEDIA	Compressed Air
APPLICATION	Food Processing
APPLICATION	Pharmaceutical
APPLICATION	Chemicals
APPLICATION	Oil & Gas
APPLICATION	Medical
APPLICATION	Clean Rooms
APPLICATION	Aircraft
VACUUM PRESSURE RATING	755 mm-Hg
WEIGHT	0.243 kg/package