



Brand of NTN corporation

Technical data

UCT217
Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC217G2, T217

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	73 mm
A1 - Width of location slot	30 mm
A2	54 mm
B - Width of Inner Ring	85,7 mm
d - Shaft diameter	85 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

G - Grease fitting	M10x1
H - Housing length, width or diameter	198 mm
H1 - Distance between location slots	173 mm
H2 - Housing height / width	124 mm
L - Housing length	260 mm
L1 - Distance attachment end face to bearing centerline	162 mm
L2 - Thickness of attachment end	29 mm
L3 - Length of guidance slot/face	157 mm
N - Mounting hole dimension	48 mm
N1 - Length of attachment slot	38 mm
N2 - Height of attachment slot	73 mm
S - Distance front side/bearing centre	34,1 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	83200000 mN
C0 - Static load rating	63800000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	10,78 kg
Recommended tightening torque for set screw	33 N-m

