

DeWalt DWB6800-B1

800W Variable Speed Blower

Introduction

The **800W Variable Speed Blower** is designed for professional dust clearance, maintenance, and heavy-duty cleaning applications. Its powerful 800W motor delivers high-performance airflow, while the variable speed control dial provides enhanced precision and tailored air control. The compact, dual-function design with an ergonomic D-handle makes it ideal for use in both blowing and suction tasks across tight jobsite spaces.

Key Features

- **Powerful 800W Motor:** Delivers high-performance airflow with an air volume of 4.5 m³/min and an air discharge pressure of 5.2 N to quickly clear dust and debris.
- **Dual Functionality:** Offers both blowing (ventilation) and suction capabilities, making it highly versatile for various cleaning tasks.
- **Variable Speed Control:** Equipped with a multi-step dial to adjust the speed smoothly from 0 to 16,000 RPM for precise air control based on the task.
- **Ergonomic Design:** Features a comfortable grip and a compact footprint that minimizes fatigue during extended use.
- **Dust Management:** Includes a detachable rubber nozzle and a dust bag to keep collected particles contained while operating in suction mode.

Specifications Table

Feature	Specification
Power Source	Battery powered (18V XR Li-ion) / 12V DC Car Adapter / Optional 240V AC Adapter
Voltage	20 v
Max Pressure (High Pressure)	11 bar (160 PSI)
Air Flow Capacity (High Pressure)	0.35 l/min @ 6.2 bar; 0.6 l/min @ 2 bar
Air Flow Capacity (High Volume)	14.7 liters per minute
Max Power	12 Watt
Product Dimensions (L x W x H)	33 x 14 x 26 cm
Weight	2.7 kg (approx.)
Noise Level (LPA)	79 dB(A)
Special Features	2-level air pressure switch, LED work light, Digital Gauge, Auto Shut-off
Material	Aluminum