

## FEATURES

- **Graphite and PTFE material:** Provides excellent chemical resistance and durability
- **Maximum operating pressure of 8500 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 280 °C:** Ensures performance in high-temperature environments
- **Rotary speed of 28 m/s:** Supports high-speed operations
- **Section size of 6.5 mm:** Fits a variety of gland and valve sizes

## RS PRO 8m Gland & Valve Packing, Graphite PTFE

RS Stock No: 606-562



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland and valve packing is designed for high-performance sealing in industrial applications. Made from a combination of graphite and polytetrafluoroethylene (PTFE), it offers excellent durability and chemical resistance. Ideal for use in high-pressure and high-temperature environments, this packing ensures reliable performance and longevity.

## General Specifications

Maximum Operating Pressure	8500 kPa
Product Type	Gland & Valve Packing
Rotary Speed	28 m/s
Section	6.5 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Graphite, Polytetrafluoroethylene

## Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------