




FAG

32321-A

Tapered roller bearing

Tapered roller bearings 323, main dimensions to DIN ISO 355 / DIN 720, separable, adjusted or in pairs

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2014)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	Standard	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	105 mm	Bore diameter
D	225 mm	Outside diameter
B	77 mm	Width, inner ring
C	63 mm	Width, outer ring
T	81.5 mm	Width, total
C _r	670,000 N	Basic dynamic load rating, radial
C _{0r}	930,000 N	Basic static load rating, radial
C _{ur}	105,000 N	Fatigue load limit, radial
n _G	3,100 1/min	Limiting speed
n _{gr}	2,220 1/min	Thermal speed rating
≈m	16 kg	Weight



SCHAEFFLER

Mounting dimensions

d _a max	128 mm	Maximum diameter of shaft shoulder
d _b min	119 mm	Minimum diameter of shaft shoulder
D _a min	185 mm	Minimum diameter of housing shoulder
D _a max	211 mm	Maximum diameter of housing shoulder
D _b min	209 mm	Minimum diameter of housing shoulder
C _a min	9 mm	Minimum axial space
C _b min	18.5 mm	Minimum axial space
r _a max	4 mm	Maximum fillet radius of shaft
r _b max	3 mm	Maximum fillet radius of housing

Dimensions

$r_{1,2 \text{ min}}$	4 mm	Minimum chamfer dimension of inner ring back face
$r_{3,4 \text{ min}}$	3 mm	Minimum chamfer dimension of outer ring back face
a	56 mm	Distance between the apexes of the pressure cones
d_1	160.85 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0.35	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1.74	Dynamic axial load factor
Y ₀	0.96	Static axial load factor

Additional information

T2GD105	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed