

Technical data


33110A

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage



VISUAL (S)



33110A

Single row tapered roller bearings

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	50 mm
D - External diameter	85 mm
B - Bearing/Inner ring width	26 mm
C - Outer ring width	20 mm
T - Total width	26 mm
d1 - External diameter inner ring	67,5 mm
a - Charge load application point	20,4 mm
rs - Min fillet radius	1,5 mm
r1s - Min fillet radius	1,5 mm
Mass	0,574 kg
ISO 355 reference	T3CE050

PRODUCT PERFORMANCE

C - Dynamic load	93,3 kN
A2 - Rating life coefficient	1
C0 - Static load	124 kN
Cu - Fatigue limit load	15,1 kN
e - Coefficient	0.41
Y0 - Static axial load coefficient	0.8
Y2 - Upper axial load coefficient	1.46
N ref - Reference thermal speed	4600 tr/min
N lim - Mechanical Limit Speed	8200 tr/min
Tmin - Min operating temperature	-40 °C



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

33110A

Single row tapered roller bearings

PRODUCT PERFORMANCE

Tmax - Max operating temperature	120 °C
---	--------

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	9.186 Hz
BPFI - Over rolling frequency on inner (60 rpm)	11.814 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	7.585 Hz
BRF - Fréquence de rotation : Élément roulant	3.793 Hz
FTF - Rotational frequency - cage (60 rpm)	0.437 Hz

ABUTMENT

da max - Max shoulder diameter IR	56 mm
db min - Min IR shoulder diameter	58,5 mm
Da min - Min shoulder diameter OR	74 mm
Da max - Max shoulder diameter OR	76,5 mm
Db min - Min OR shoulder diameter	82 mm
Ca - Min clearance	4 mm
Cb - Min clearance	6 mm
ra max - Max fillet radius	1,5 mm
r1a - Max fillet radius	1,5 mm

ESHOPDONOTDISPLAY

Reference	33110A
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
KIZEI	Non/No
TOPLINE	Non/No
ULTAGE	Non/No



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
- Contact angle	15.333 °

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X_o	Y_o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table