





Test probes

**PRUEF 2700**



Product	PRUEF 2700
description	Safety test probe with dual function. Tip for penetrating oxide layers and 4 mm diameter pin for insertion in sockets. 4 mm diameter brass socket connection. Connects with safety measuring leads.
operating instruction	BA463
article-no. / *colour	9723191xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black         </div> <div style="text-align: center;">  01 red         </div> </div> <div style="text-align: right; border: 1px solid black; padding: 2px; width: fit-content;">Ni</div>
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage <sup>(1)</sup>	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT II
rated current <sup>(1)</sup> (consider derating curve)	32 A
material socket	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
standard	IEC 61010

4 mm safety system

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges  
stand: 19.06.2019