



Main

Range	Easy TeSys
Range of product	Easy TeSys Protect
Product or component type	Differential thermal overload relay
Device short name	LRN
Relay application	Motor protection
Phase failure sensitivity	Tripping current I 30 % of I _r on one phase, the others at I _r conforming to IEC 60947-4-1
Colour	Grey (RAL 7011)

Complementary

Product compatibility	LC1N06...38
Range compatibility	EasyPact EasyPact D3N LC1N
Network type	AC
Network frequency	50...60 Hz
Mounting support	Under contactor Plate, with specific accessories Rail, with specific accessories
Thermal overload class	Class 10A conforming to IEC 60947-4-1
Signalling function	Relay trip indicator
Thermal protection adjustment range	0.4...0.63 A
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
Mechanical robustness	Shocks: 6 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 GN conforming to IEC 60068-2-6
Auxiliary contact composition	1 NO + 1 NC
[I _{th}] conventional free air thermal current	5 A for signalling circuit
[U _e] rated operational voltage	<= 690 V AC
Associated fuse rating	2 A gG for power circuit 1 A aM for power circuit 5 A gG for signalling circuit
[U _i] rated insulation voltage	690 V conforming to IEC 60947-4-1
[U _{imp}] rated impulse withstand voltage	6 kV
Local signalling	Trip indicator
Control type	Push-button red stop: Push-button green reset:
Temperature compensation	-20...60 °C
Connections - terminals	Power circuit: screw clamp terminals 1 1.5...6 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1...6 mm ² - cable stiffness: solid without cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible without cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: solid without cable end
Recommended tightening torque	1.7 N.m - on screw clamp terminals

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Height	44.5 mm
Width	45 mm
Depth	70 mm
Net weight	0.124 kg

Environment

Standards	GB 14048 IEC 60947-4-1
Product certifications	CCC
Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C without derating conforming to IEC 60947-4-1 -20...70 °C with derating
Ambient air temperature for storage	-60...80 °C
Fire resistance	850 °C conforming to IEC 60068-2-1
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Electromagnetic compatibility	Surge withstand: 6 kV conforming to IEC 60801-5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.31 cm
Package 1 Width	8.057 cm
Package 1 Length	8.341 cm
Package 1 Weight	147.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	33
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.211 kg
Unit Type of Package 3	P06
Number of Units in Package 3	660
Package 3 Height	90.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	114.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins