



Main

Range	New Unica
Product or component type	Pull string switch
Device presentation	Mechanism
Device application	Control
Switch function	1-pole 2-way
Rated current	10 A
Actuator	Cord push-button
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)

Complementary





Technology type	Electromechanical
Cable length	1 m
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Opening distance	> 3 mm
Connections - terminals	Screwless terminals
Cable cross section	2.5 Mm ² flexible cable 2.5 mm ² rigid cable
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Electrical durability	20000 cycles, cos phi = 0.6
Dielectric strength	2000 V
Insulation resistance	> 5 MOhm at 500 V
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing CuZn37: terminals PBT (polybutylene terephthalate) GF30: release button
Standards	IEC 60669-1
Directives	2014/35/EU - low voltage directive
Product certifications	NF[RETURN]CE[RETURN]AENOR[RETURN]EAC
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Embedding depth	21.15 mm
Depth	47 mm
Width	45 mm
Height	45 mm
Net weight	0.035 kg
Surface treatment	Painted

Surface finish	Matt
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins