


Features

- FeCu-Ni "J" Type Thermocouples
- Max. operating temperature 400°C
- 1/4" x 19" connector
- Protection tube AISI304(DIN1.4301) Stainless Steel
- Sensor type DIN/IEC-584 "J" FeCu-Ni
- Cable type Fiber glass+Fiber glass+Braided
- Immersion Length 100mm
- Cable Length 2meter

RS PRO Standard Bayonet Type Thermocouples With 1/4" x 19" Connector

RS Stock No: 0350429



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Standard Bayonet "J" Type Thermocouples Temperature Sensor

Diameter(M): 6mm

Immersion Length(L): 100mm

Cable Length(K): 2m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


General Specifications

Max. Operating Temperature	-50 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	"J" Type Thermocouples (DIN/IEC-584)
Protection tube material	AISI304(DIN1.4301) Stainless Steel
Connector	Standard 1/4 x 19"

Mechanical Specifications

Diameter (M)	6mm
Immersion Length (L)	100mm
Cable Length (K)	2m

Electrical Connection



Thermoelement Connections

