

86566-2 ✓ ACTIVE

TE Internal #: 86566-2

Socket Contact, 26 – 22 AWG, .12 – .4 mm<sup>2</sup> Wire, Gold (Au) / Gold

Flash over Palladium Nickel, Discrete Wire, Crimp, Phosphor

Bronze, Signal

[View on TE.com >](#)



Connectors > Contacts > Connector Contacts > 2.54mm FFC Connectors Socket Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold (Au), Gold Flash over Palladium Nickel**

Compatible With Wire & Cable Type: **Discrete Wire**

Wire Size: **.12 – .4 mm<sup>2</sup>**

[All 2.54mm FFC Connectors Socket Contacts \(33\)](#)

## Features

### Configuration Features

|                                   |               |
|-----------------------------------|---------------|
| Compatible With Wire & Cable Type | Discrete Wire |
|-----------------------------------|---------------|

### Contact Features

|   |   |
|---|---|
|   | 15 µin                                      |
| Contact Underplating Material                 | Nickel                                      |
| PCB Contact Termination Area Plating Material | Gold Flash                                  |
| Contact Type                                  | Socket                                      |
| Contact Mating Area Plating Material          | Gold (Au), Gold Flash over Palladium Nickel |
| Contact Base Material                         | Phosphor Bronze                             |
| Contact Current Rating (Max)                  | 2 A   |

### Termination Features

|                                    |              |
|------------------------------------|--------------|
| Termination Method to Wire & Cable | Crimp        |
| Product Terminates To              | Wire & Cable |

### Dimensions

|                                      |                                |
|--------------------------------------|--------------------------------|
| Accepts Conductor Width              | 1.27 mm, 1.82 mm               |
| Compatible Insulation Diameter Range | 1.02 – 1.42 mm [.04 – .056 in] |
| Wire Size                            | .12 – .4 mm <sup>2</sup>       |

### Usage Conditions

|                             |                             |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -65 – 105 °C [-85 – 221 °F] |
|-----------------------------|-----------------------------|



### Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

### Packaging Features

|                  |      |
|------------------|------|
| Packaging Method | Reel |
|------------------|------|

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not applicable for solder process capability  |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Customers Also Bought



## Documents

### Product Drawings

[FFC RECP CONT PLTD 1 FULL AU](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_86566-2\\_AN.2d\\_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_86566-2\\_AN.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_86566-2\\_AN.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



### Product Specifications

#### Application Specification

English

#### Application Specification

English

---

### Instruction Sheets

#### Instruction Sheet (U.S.)

English

#### Extraction Tool for Flexible Flat Cable (FFC)

English

#### Instruction Sheet (U.S.)

English

#### Extraction Tools

English