





Technical data

62/28NRC3

Single row deep groove ball bearings

Deep groove ball bearing, radial contact, pressed steel cage, snap ring & groove on outer diameter, open

VISUAL (S)



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	28 mm
D - External diameter	58 mm
B - Bearing/Inner ring width	16 mm
a min - Min position Groove	2,31 mm
a max - Max position groove	2,46 mm
rs - Min fillet radius	1 mm
rNs - Min fillet radius	0,5 mm
D3 - Max bottom groove diameter	55,6 mm
b min - Min groove width	1,35 mm
b max - Max groove width	1,65 mm
r0 max - Max bottom groove radius	0,4 mm
D4 max - Max outer diameter of assembled stop ring	63,7 mm
f - Stop ring thickness	1,12 mm
Snap ring reference	R58
Radial clearance class	C3
Mass	0,171 kg

PRODUCT PERFORMANCE	
C - Dynamic load	19800000 mN
C0 - Static load	9750000 mN
Cu - Fatigue limit load	720000 mN
f0 - Coefficient	13.4
N lim - Oil lubrication limit speed	84000 °/s



PRODUCT PERFORMANCE

N lim - Grease lubrication limit speed	72000 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	33 mm
Da max - Max shoulder diameter OR	53 mm
ra max - Max shaft & housing fillet radius	1 mm
rNa max - Max fillet radius on segment side	0,5 mm
Ca min - Mini segment position	3,43 mm
Ca max - Max segment position	3,58 mm
Db min - Min stop ring position diameter	64,5 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.6	0.5

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$

