

## QVNU2.E76126 Protectors, Supplementary - Component

[Page Bottom](#)

### Protectors, Supplementary - Component

[See General Information for Protectors, Supplementary - Component](#)

ABB STOTZ-KONTAKT GMBH  
EPPELHEIMER STR 82  
69123 HEIDELBERG, GERMANY

E76126

Accessory auxiliary contacts, Cat. Nos. S2-H, S2-S/H, S2-H03kL, S2-H12kL, S2-H30kL, S2-H21kL, S201, S2C-A1, S2C-A2; Cat. Nos. S2C-S/H6R, S2C-H6R; Cat. Nos. S2C-H01, S2C-H10.

Cat. Nos. SC2-H6-11R, SC2-H6-20R, SC2-H6-02R.

Accessory auxiliary switches, Cat. Nos. S2C-H11R, S2C-H20R and S2C-H02R.

Accessory busbars, Cat Nos. KS, SZ followed by additional suffixes; Cat. Nos. PSB3UL, -53UL, SZ-PSB followed by 2 or 3 digits; Model VB45.32; end cap Cat. No. PSB-END; stab cover Cat. No. SZ-BSK; Cat. No. PS followed by 1, 2, 3 or 4, followed by digits up to 60 with or without additional digits and/or letters.

Accessory shunt trips, Cat Nos. S2-A1, S2-A2, S2C-A1, S2C-A2.

Auxiliary contacts , Models S290-H11, S290-S11.

Supplementary protectors, Cat. Nos. S221, S222, S223 followed by K, followed by a number between .02, 0.3, 0.5, 0.75, 1, 1.6, 2, 3, 4, 6, 8, 10, 16, 20, 25, 32, 40, 50 and 63. All Cat. Nos. may have suffix NA.

Cat. Nos. S201, S202, S203, S204, followed by letter B or C, followed by a number 6 to 63. All Cat. Nos. may have suffix NA.

Cat. No. S200 followed by additional letters.

Series S280, Cat. Nos. S281, S282, S283, S284 followed by D, DS, K, W, L, UCK, UCZ or Z, followed by a number between .02 and 63 incl. May have suffix NA.

Series S 291 B 80, S 291 B 100, S 291 B 125, S 291 C 80, S 291 C 100, S 291 C 125, S 291 D 80, S 291 D 100, S 292 B 80, S 292 B 100, S 292 B 125, S 292 C 80, S 292 C 100, S 292 C 125, S 292 D 80, S 292 D 100, S 293 B 80, S 293 B 125, S 293 C 80, S 293 C 100, S 293 C 125, S 293 D 80, S 293 D 100, S 294 B 80, S 294 B 100, S 294 B 125, S 294 C 80, S 294 C 100, S 294 C 125, S 294 D 80, S 294 D 100.

Series S200P, Cat. Nos. S201P, S202P, S203P, S204P followed by B, C, D, K or Z, followed by a number between .02 and 63.

Cat. Nos. S201, S202, S203, and S204 followed by K followed by a number from 5, 15, 30, 60 or followed by C, D, K or Z followed by a number from 0.5 or 1.6 or f/b B, C, D, K or Z followed by 1, 2, 3, 4, 6, 8, 10, 13, 16, 20, 25, 32, 40, 50, 63 may be followed by additional suffixes. Cat. Nos. with Suffix H01 or H10 have factory installed R/C auxiliary contact.

Cat. Nos. S20, followed by 1, 2, 3 or 4, followed by P R-K or M R-K, followed by a number from 0.2 to 63, may be followed by additional suffixes.

Cat. Nos. S201M, S202M, S203M, S204M followed by C, D, K or Z, followed by a number from 0.5 or 1.6 or followed by B, C, D, K or Z, followed by a number from 1 to 63 or followed by K followed by a number from 5, 15, 30, 60, may be followed by additional suffixes. Cat. Nos. with Suffix H01 or H10 have factory installed R/C auxiliary contact. All catalog numbers may have Suffix NA.

Cat. Nos. RP201M, RP202M, RP203M, followed by B, C, or D, followed by a number from 0.5 to 63, may be followed by additional suffixes. Cat. Nos. with Suffix H01 or H10 have factory installed R/C auxiliary contact.

Cat. Nos. SP201M, SP202M, SP203M, SP204M, followed by B, C, D, K or Z, followed by a number from 0.2 to 63, may be followed by additional suffixes. Cat. Nos. with Suffix H01 or H10 have factory installed R/C auxiliary contact. All catalog numbers may have Suffix NA.

Cat. No.	Type	UG	FW	Max V	Max Amps	TC	OL	SC	Operation
S200-B, -C, -D, -K, -Z (one pole devices)	OC	A	0	277	63	0	0	6kA,C1	
S200-B, -C, -D, -K, -Z (multi pole devices)	OC	A	0	480Y/277	63	0	0	6kA,C1	
S201-B, -C, -D, -K, -Z	OC	A	0	277	63	0	0	6kA,U1	
S200-B, -C, -D, -K, -Z (one pole devices)	OC	A	0	120	63	0	0	10kA, C1	
S202, S203, S204-B, -C, -D, -K	OC	A	0	480Y/277	63	0	0	6kA, U1	
S200-B, -C, -D, -K, -Z (multi pole devices)	OC	A	0	240	63	0	0	10kA,U1	
S200-B, -C, -D, -K, -Z (one pole devices)	OC	A	0	60 dc	63	0	0	10kA, U1	
S200-B, -C, -D, -K, -Z (multi pole devices)	OC	A	0	110 dc	63	0	0	10kA,U1	
S20 followed by 1, followed by P R-K or M R-K	OC	A	0	277	63	0	0	10kA,U1	
S20 followed by 2, 3 or 4, followed by P R-K or M R-K	OC	A	0	480Y/277	63	0	0	10kA,U1	
S200M-B, -C, -D, -K, -Z (one pole devices)	OC	A	0	60 dc	63	0	0	10kA, U1	
S200M-B, -C, -D, -K, -Z (multi pole devices)	OC	A	0	125 dc	63	0	0	10kA, U1	

S200M-B, -C, -D, -K, -Z (one pole devices)	OC	A	0	277	63	0	0	6kA, U1	
S200M-B, -C, -D, -K, -Z (multi pole devices)	OC	A	0	480Y/277	63	0	0	6kA, U1	
SP20 followed by 1, followed by M and -B, -C, -D, -K or -Z (one pole devices)	OC	A	0	48V dc	63	0	0	10kA, U2	
SP20 followed by 2,3,4, followed by M and -B, -C, -D, -K or -Z (multi pole devices)	OC	A	0	96V dc	63	0	0	10kA, U2	
SP20 followed by 1, followed by M and -B, -C, -D, -K or -Z (one pole devices)	OC	A	0	277	63	0	0	10kA, U2	
SP20 followed by 2,3,4, followed by M and -B, -C, -D, -K or -Z (multi pole devices)	OC	A	0	480Y/277	63	0	0	10kA, U2	
S221	OC	F	0	347	63	2	0	3kA,U1	
S222, S223	OC	F	0	600	63	2	0	3kA,U1	
S281	OC	A	3	277	63	1	0	6kA,U1	
				120				10kA,U1	
S282, S283, S284	OC	A	3	480	63	1	0	6kA,U1	
				240				10kA,C1	
S200P-B, -C, -D	OC	A	3	277	25	1	0	10kA,C2	Trip-free
S200P-K, -Z	OC	A	3	277	25	0	0	10kA,C2	Trip-free
S200P-B, -C, -D	OC	A	3	480Y/277	25	1	0	10kA,C2	Trip-free
S200P-K, -Z	OC	A	3	480Y/277	25	0	0	10kA,C2	Trip-free
S200P-K, -Z	OC	A	3	277	32-63	0	0	10kA,U1	Trip-free
S200P-B, -C, -D	OC	A	3	480Y/277	32-63	1	0	10kA,U1	Trip-free
S200P-K, -Z	OC	A	3	480Y/277	32-63	0	0	10kA,U1	Trip-free
S200P-B, -C, -D	OC	A	3	277	32-63	1	0	10kA,U1	Trip-free
S200P-K, -Z	OC	A	3	277	32-63	0	0	6kA,C2	Trip-free
S200P-B, -C, -D	OC	A	3	480Y/277	32-63	1	0	6kA,C2	Trip-free
S200P-K, -Z	OC	A	3	480Y/277	32-63	0	0	6kA,C2	Trip-free
S200P-B, -C, -D	OC	A	3	277	32-63	1	0	6kA,C2	Trip-free
S 291 B 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 B 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 B 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 C 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 C 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 C 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 D 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 291 D 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 B 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 B 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 B 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 C 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	

									U214kA,U2
S 292 C 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 C 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 D 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 292 D 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 B 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 B 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 C 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 C 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 C 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 D 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 293 D 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 B 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 B 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 B 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 C 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 C 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 C 125	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 D 80	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
S 294 D 100	OC	A	0	480	125	2	0	5kA,U27.5kA,	
								U214kA,U2	
RP20 followed by 1, followed by M, followed by B, C or D	OC	A	3	48 dc	63	1	0	10kA, U2	
RP20 followed by 2, followed by M, followed by B, C or D	OC	A	3	96 dc	63	1	0	10kA, U2	
RP20 followed by 1, followed by M, followed by B, C or D	OC	A	3	277	0.5-32	1	0	10kA, U2	
RP20 followed by 2 or 3, followed by M, followed by B, C or D	OC	A	3	480Y/277	0.5-32	1	0	10kA, U2	
RP20 followed by 1, followed by M, followed by B, C or D	OC	A	3	277	35-63	1	0	5kA, U2	
RP20 followed by 2 or 3, followed by M, followed by B, C or D	OC	A	3	480Y/277	35-63	1	0	5kA, U2	

S20, followed by 1, 2, 3 or 4, followed by MUC, followed by -K, followed by a number from 0.2 up to 63	OC	A	0	277	0.2-63	0	0	6kA, U2
	OC	A	0	480Y/277	0.2-63	2	0	6kA, U2
	OC	A	0	250 dc	0.2-63	0	0	10kA, U1
	OC	A	0	500 dc	0.2-63	2	0	10kA, U1
S20, followed by 1, 2, 3 or 4, followed by MUC, followed by -Z, followed by a number from 0.5 up to 63	OC	A	0	277	0.5-63	0	0	6kA, U2
	OC	A	0	480Y/277	0.5-63	2	0	6kA, U2
	OC	A	0	250 dc	0.5-63	0	0	10kA, U1
	OC	A	0	500 dc	0.5-63	2	0	10kA, U1
S20, followed by 1, 2, 3 or 4, followed by MUC, followed by -C, followed by a number from 0.5 up to 63	OC	A	0	277	0.5-63	0	0	6kA, U2
	OC	A	0	480Y/277	0.5-63	2	0	6kA, U2
	OC	A	0	250 dc	0.5-63	0	0	10kA, U1
	OC	A	0	500 dc	0.5-63	2	0	10kA, U1
S20, followed by 1, 2, 3 or 4, followed by MTUC, followed by -K, followed by a number from 0.2 up to 63	OC	A	0	277	0.2-63	0	0	6kA, U1
	OC	A	0	480Y/277	0.2-63	2	0	6kA, U1
	OC	A	0	250 dc	0.2-63	0	0	10kA, U1
	OC	A	0	500 dc	0.2-63	2	0	10kA, U1
S20, followed by 1, 2, 3 or 4, followed by MTUC, followed by -Z, followed by a number from 0.5 up to 63	OC	A	0	277	0.5-63	0	0	6kA, U1
	OC	A	0	480Y/277	0.5-63	2	0	6kA, U1
	OC	A	0	250 dc	0.5-63	0	0	10kA, U1
	OC	A	0	500 dc	0.5-63	2	0	10kA, U1
S20, followed by 1, 2, 3 or 4, followed by MTUC, followed by -C, followed by a number from 0.5 up to 63	OC	A	0	277	0.5-63	0	0	6kA, U1
	OC	A	0	480Y/277	0.5-63	2	0	6kA, U1
	OC	A	0	250 dc	0.5-63	0	0	10kA, U1
	OC	A	0	500 dc	0.5-63	2	0	10kA, U1

Marking: Company name and catalog number, type or series designation.

Last Updated on 2014-11-13

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2015 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".