

Eaton 186904

Catalog Number: 186904

Eaton Moeller® series ZFS Clamp with label, For use with T5, T5B, P3, 88 x 27 mm, Inscribed with "Supply disconnecting device" (IEC/EN 60204), Language Turkish

General specifications



Product Name	Catalog Number
Eaton Moeller® series ZFS Accessory	186904
Clamp with label	EAN
	4015081819560
Product Length/Depth	Product Height
88 mm	3 mm
Product Width	Product Weight
27 mm	0.004 kg
Compliances	
CE	

Product specifications

Used with

For mechanisms with padlocking feature

T5B

Type

Front plates

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Not applicable.

10.12 Electromagnetic compatibility

Not applicable.

10.13 Mechanical function

Not applicable.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Resources

Brochures

[Brochure - T Rotary Cam switch and P Switch-disconnector](#)

Catalogs

[P Switch-disconnectors and T Rotary cam switches catalogue CA042001EN](#)

Installation videos

[Eaton's P Switch-disconnectors used in a factory](#)

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

Label mount

Insert label

Accessory/spare part type

Device labeling system

Ambient operating temperature - max

50 °C

Ambient operating temperature - min

-25 °C

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

0 A

Static heat dissipation, non-current-dependent P_{vs}

0 W

Language

Turkish

Connection type

Plug-in

Functions

Add-on front plates

Inscription

Supply disconnecting device



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia