

INB IO 10-6 GY - Insertion bridge



3246917

<https://www.phoenixcontact.com/gb/products/3246917>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, Bridging in the terminal point, latching in the terminal housing, number of positions: 10, color: gray

Commercial data

Item number	3246917
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE1Z2X
Product key	BEKZ2X
GTIN	4046356706179
Weight per piece (including packing)	4.43 g
Weight per piece (excluding packing)	4.43 g
Customs tariff number	85366990
Country of origin	PL

INB IO 10-6 GY - Insertion bridge



3246917

<https://www.phoenixcontact.com/gb/products/3246917>

Technical data

Product properties

Product type	Insertion bridge
Number of positions	10
Potentials	10

Material specifications

Color	gray (RAL 7042)
Material	Cu
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

INB IO 10-6 GY - Insertion bridge



3246917

<https://www.phoenixcontact.com/gb/products/3246917>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

INB IO 10-6 GY - Insertion bridge



3246917

<https://www.phoenixcontact.com/gb/products/3246917>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk