

Price\* : 16.12 GBP



### Main

Range	TeSys
Device short name	VZ
Product or component type	Additional earthing block
Performance level	High performance
Contacts type and composition	Without
Product compatibility	V3 V4
Network type	AC DC
Network frequency	50/60 Hz

### Complementary

Mounting location	Left Right
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	80 A
Connections - terminals	Screw clamp terminals
Height	83 mm
Width	20 mm
Depth	46 mm
Product weight	0.1 kg

### Environment

Standards	IEC 60947-3
Product certifications	CSA GL UL
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz 5 gn IEC 60068-2-6

Shocks 11 ms 15 gn IEC 60068-2-27

---

Ambient air temperature for operation -20...50 °C

---

Fire resistance 960 °C conforming to IEC 60695-2-1

---

### Contractual warranty

---

Warranty period 18 months

---