


C44A, Film, Metallized Polypropylene, Power, 60 uF, 5%, 330 VAC, 600 VDC



Dimensions

D	60mm +/-0.5mm
L	138mm +/-2mm
S	22.3mm +/-0.5mm

Packaging Specifications

Mounting:	Bolt - M12x12.5
Packaging:	Bulk, Bag
Packaging Quantity:	16

General Information

Supplier:	KEMET
Series:	C44A
Dielectric:	Metallized Polypropylene
Style:	Can
RoHS:	Yes
Lead:	Threaded Studs M6
Miscellaneous:	Thermal Resistance = 3.1 C/W

Specifications

Capacitance:	60 uF
Capacitance Tolerance:	5%
Voltage AC:	330 VAC
Voltage DC:	600 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70°C
Max dV/dt:	20 V/us
Resistance:	5 mOhms (TYP)
Ripple Current:	32 Amps, 1200 Amps (Peak)