



**Part Number :** 908140208

**Product Description :** Picoflex PF-50 Header with PCB Pegs, Vertical, Standard Profile, Surface Mount, Tin (Sn) Plated, 8 Circuits, Tape and Reel, Natural



**Series Number :** 90814

**Status :** Active

**Product Category :** PCB Headers and Receptacles

---

## Documents & Resources

### Drawings

[908140208\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[908140000-AS-000.pdf](#)

[PK-90814-001-001.pdf](#)

[PS-99020-0011-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 33; 34; 47; 44; 3; 57; 63
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## **Part Details**

### **General**

Status	Active
Category	PCB Headers and Receptacles
Series	90814
Description	Picoflex PF-50 Header with PCB Pegs, Vertical, Standard Profile, Surface Mount, Tin (Sn) Plated, 8 Circuits, Tape and Reel, Natural
Application	Signal, Wire-to-Board
Comments	Standard Profile
Component Type	PCB Header
Product Name	Picoflex
UPC	800753656062

### **Agency**

UL	E29179
----	--------

### **Electrical**

Current - Maximum per Contact	1.2A
Voltage - Maximum	250V

## Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.576/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	3.048µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

## Solder Process Data

Max-Duration	3
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Picoflex PF-50 Low Profile IDT Receptacles	<u>90327</u>

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Picoflex PF-50 Connectors, 4-26 Circuits	<u>690081070</u>

---

This document was generated on Sep 23, 2025