


## LED Spot PAR16 Glass GU10 2.4W (50W) 380lm 840 38D

Article number 146182

BAI BaiSpot Class B LED Spot PAR16 GU10 2.4W (50W) 380lm 4000K 38° Glass Reflector 235V 50x55mm LED-lamp

The so-called LED spots from the BaiSpot series are characterized by a much longer lifespan and significantly less energy consumption than their halogen predecessors. Due to the compact design, they are easily interchangeable. Spots are mainly used to provide directed light from the ceiling or wall. This glass version literally and figuratively has an extra beautiful appearance because the part through which the light shines is made entirely of glass. This version of the BaiSpot has energy class B so is even more energy efficient. Ambient temperature range: -20°C to +40°C.



### General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	146182
Brand	Bailey
Productseries	BaiSpot LED MV
Product type	GU10 Glass

## ETIM specifications

Nominal voltage [V]	220 - 240
Nominal current [mA]	27 - 27
Power factor	0.4
Lamp power [W]	2.4 - 2.4
Voltage type	AC
Luminous flux [lm]	380 - 380
Rated luminous flux according to IEC 62612 [lm]	380
Lamp efficacy [lm/W]	158
Luminous intensity [cd]	650
Colour rendering index CRI	80-89
Lamp shape	Reflector
Filament lamp	No
Type of glass/cover	Prism
Colour of light according to EN 12464-1	Neutral white 3300-5300 K
Socket	GU10
Colour	Other
Colour temperature [K]	4000 - 4000
Colour housing	Colourless
Beam angle [°]	38 - 38
Colour consistency (McAdam ellipse)	SDCM6
Dimmable	No
Diameter [mm]	50
Length [mm]	55
Degree of protection (IP)	IP20
Lamp designation	PAR16
Energy efficiency class	B
Min. number of switching cycles	25000
Weighted energy consumption in 1000 hours [kWh]	3
Average nominal lifespan [h]	50000
Remote operation possible	No
With remote control	No
Photobiological safety according to EN 62471	RG1
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No