

Outdoor IP Dome IR 6MPx

Art. no. IPCA76500

Page 1 of 4



- 6 megapixel resolution: 3072 x 2048 @ 24 fps
- 2.8–12.0 mm motorised zoom lens with automatic focussing
- Day & night camera with integrated IR LEDs (30 m)
- DWDR function to compensate for image contrasts
- Integrated video content analysis (VCA) (e.g. tripwire detection, intrusion detection, object counting)
- Integrated microSD card slot for edge recording
- Integrated ROI function that saves on bandwidth and storage space
- Automatic backup recording to ensure uninterrupted recording
- Weatherproof housing that is protected against vandalism with IP66/IK10 protection class

This 6megapixel IP dome is designed to take on even the most challenging of monitoring applications. Its resolution of 3072x2048pixels (6MPx) allows it to cover expansive areas, while the motorised zoom lens enables versatile monitoring and exceptional flexibility in selecting an installation location.

Detailed monitoring of moving objects

The camera provides 6megapixel video streams at 25fps. Boasting incredibly high resolution and real-time recording performance, it guarantees extremely clear recordings, for example in the monitoring of perimeters of large premises.

24/7 robust outdoor surveillance in HD

The weatherproof IP66 housing with IK10 shock resistance provides optimum protection against tampering and vandalism. Integrated IR LEDs provide excellent images both during the day and at night. Plus, cutting-edge motion detection and backlight compensation functionalities are integrated – ideal for handling glare in outdoor areas or monitoring access roads.

Unbeatable overview and freely controllable angle of view

The autofocus motorised zoom lens can be adjusted to the desired angle of view at the touch of a button. Its focal length of between 2.8 and 12mm covers a range of between 30° and 95° (4.2x optical zoom).

Outdoor IP Dome IR 6MPx

Art. no. IPCA76500

Page 2 of 4

Decentralised video content analysis (VCA) – in the camera itself

The dome offers VCA functions such as tripwires, intrusion detection and face detection, all without the need for any VMS software. This saves on bandwidth, hard disk space and additional costs, while also making the evaluation of recordings faster.

Easy set-up – innovative user management

The practical installation wizard ensures quick and easy set-up. Innovative user management also facilitates user authorisation configuration that is tailored to your individual security needs.

The effective IR range will depend on the installation location. If there are surfaces that absorb light or no objects that reflect IR light in the field of view, the IR range will be reduced and/or the video image will be too dark. Reflective objects in the immediate vicinity of the camera (e.g. roof gutter or wall) may also result in the reflection of IR light, which can disturb the image.

Outdoor IP Dome IR 6MPx

Art. no. IPCA76500

Page 3 of 4

Technical Data:

IK protection class	10
ONVIF	Profile S
Image enhancement	DWDR, BLC, HLC, Defog, Region of Interest
Video Content Analysis (VCA)	Tripwire Detection, Intrusion Detection, Face Detection, Object Counting
Other features	Auto Backup Recording
Dimensions	LxWxH (235x235x210) mm
Alarming	E-Mail, NAS, FTP, Relais
Connections	1 x RJ45, 1 x DC, 1 x video output, 1 x audio output, 1 x audio input, 1 x alarm input, 1 x alarm output
Number of users	10
Number of presets	3
Audio	2-Way Audio (over Browser, CMS)
Resolution modes	3072 x 2048, 3072 x 1728, 2560 x 2048, 2560 x 1920, 2048 x 1536, 1920 x 1080, 1280 x 720, 704 x 576, 320 x 240 pixel
Motion detection	1
Image sensor	1/1.8" Sony Exmor R™ STARVIS™ CMOS
Pixels (effective)	3072 x 2048 pixel
Frame rate	24 (3072x2048) / 25 (3072x1728) fps
Width	235 mm
Focal length	2,8 – 12,0 mm
Gross weight	1,95 kg
Dynamic range (WDR)	70 dB
Electronic shutter	1 – 1/100,000 s
Functions	Scene Change Detection, Cover Detection, Defocus Detection, IPC Hot Spare
Backlight compensation	DWDR, BLC, HLC
Height	210 mm
Horizontal angle of view	30,5 – 94,5 °
IR range (up to)	30 m

Compatible with	ABUS VMS (no VCA functions), ABUS NVR (from V3.3.4), Hybrid DVR (from V3.3.4)
Length	235 mm
Power consumption	17 W
Max. resolution @ frame rate	3072 x 2048 @ 24 fps
Max. operating temperature	60 °C
Max. humidity	95 %
Min. operating temperature	-30 °C
Minimum illumination (color)	0,014 lx
Minimum illumination (IR)	0 lx
Video network bandwidth	32 kBit/s – 16 MBit/s
Network access	RJ45
LAN network access	RJ45
Network camera protocols	TCP/IP, UDP, IPv4/v6, HTTP, HTTPS, FTP, SMTP, UPnP, DNS, DynDNS, ABUS Server, NTP, RTSP, DHCP, ONVIF, SNMP, QoS, 802.1X, PSIA
Lens	Motor-Zoom
Optical zoom	4,2 x
PoE	IEEE 802.3af
Private zones	4
Noise reduction	3D-DNR, 2D-DNR
IP protection class	66
AC voltage supply	24 (+/-10 %) V
DC voltage supply	12 (+/-10 %) V
Storage medium	microSD card, 128 GB (option)
Power consumption	1.000 mA
Day/night switching	Electromechanically removable IR cut filter (ICR), colour/B&W
Supported browsers	IE10, IE11, Firefox
Encryption	HTTPS
Video compression	H.264, MJPEG

Outdoor IP Dome IR 6MPx

Art. no. IPCA76500

Page 4 of 4

Technical Data:

Video system	IP
--------------	----

White balance	AWB, manual
Certifications	CE, CTick, RoHS, Reach