

U-17



AG Neovo's most eco-minded display with unmatched durability and power efficiency in a stylish design ideal for the busiest multi-user environments.

With a bright 17-inch screen, stereo speakers, side-mount headphone jack and USB port, the U-17's multimedia feature set is matched only by its breakthrough power-saving technology. Reduce power consumption up to 50% compared to standard LCD monitors (67% versus CRTs), or cut power usage to zero with EcoSwitch. Add durable touch-sensor controls, best-in-class NeoV™ Optical Glass, and the U-17 easily becomes the smartest, most eco-friendly choice of professionals.

- > NeoV™ Optical Glass
- > Contemporary & professional design
- > 1280 x 1024 resolution, 1000:1 contrast ratio and 3ms response
- > Eco-friendly: Slash CO₂ emissions up to 50%; Recyclable materials and green design
- > Energy efficient: Cut power bills up to 50%; Zero-watt consumption with EcoSwitch
- > Built-in headphone jack and stereo speakers
- > Wear-resistant touch sensor controls
- > Easy-access USB port (pass through)
- > New intuitive OSD with settings lock
- > Dual PC inputs: VGA and DVI
- > Kensington® security socket
- > VESA standard wall mount



NeoV™ Optical Glass - The most
trusted hard glass protection available.
Only on AG Neovo displays

U-17

Specifications

U-17

Panel	Panel Type	TFT LCD
	Panel Size	17.0" (432 mm)
	Max. Resolution	SXGA 1280 x 1024
	Pixel Pitch	0.264 mm
	Brightness	250 cd/m ² (Typical)
	Contrast Ratio	1000:1 (Typical)
	Viewing Angle (H/V)	170°/160° (Typical)
	Display Colour	16.7M
	Response Time	3 ms (GTG)z
Frequency (H/V)		H: 24 kHz - 81 kHz V: 56 Hz - 75 Hz
Input	Analogue	15-Pin D-Sub
	Digital	24-Pin DVI-D
Audio	Audio In	3.5 mm Audio Line-in
	Audio Out	3.5 mm Headphone Jack
	Speaker	1W x 2
Power	Power Supply	Internal
	Power Requirements	AC 100 - 240 V, 50 - 60 Hz
	Consumption	< 20 W (On)
		< 0.5 W (Stand-by) < 0.5 W (Off) = 0 W (EcoSwitch off)
NeoV™ Optical Glass	Thickness	3.0 mm (0.12")
	Reflection Rate	< 1%
	Transmission Rate	> 96%
	Coating Hardness	> 9H
Plug & Play	VESA	DCC 2B, DDC/CI
Operating Conditions	Temperature	0 °C ~ 40 °C
	Humidity	10% ~ 90%
Storage Conditions	Temperature	-20 °C ~ 60 °C
	Humidity	5% ~ 95%
Mounting	VESA FPMPI	Yes (100 x 100mm)
Tilt	Tilt	0° ~ +20°
Dimensions	Product (W x H x D)	397 x 390 x 174 mm (15.6" x 15.4" x 6.9")
	Packaging (W x H x D)	480 x 460 x 145 mm (18.9" x 18.1" x 5.7")
Weight	Product	5.7 kg (12.5 lbs)
	Packaged	7 kg (15.4 lbs)
Regulation Approval	Certifications & Compliance	CB, FCC, CE, GOST-R, WEEE, Energy Star, RoHS, REACH
Accessories	Supplied	CD ROM (user manual and drivers), audio cable, AC power cord and 15-Pin D-Sub cable



Side-mount headphone jack, USB port and built-in stereo speakers for multimedia convenience



Durable, long-lasting touch sensor controls won't wear out like mechanical buttons



NeoV™ Optical Glass protects against scratches, impacts and other physical damage



Slash power bills and CO emissions by up to 50% (67% versus CRTs); EcoSwitch cuts power usage to zero when off

