



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **8**

Number of Rows: **2**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Loaded Positions	8
Number of Power Positions	0
PCB Mount Orientation	Vertical
Number of Positions	8
Number of Rows	2

Electrical Characteristics

--	--



Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.762 μm[30 μin]
Contact Mating Area Plating Material Thickness	2.03 μm[80 μin]
PCB Contact Termination Area Plating Material Thickness	2.03 μm[80 μin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	9 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Keyed
PCB Mount Retention Type	Boardlock
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Nylon
Centerline (Pitch)	4.2 mm[.165 in]

Dimensions

Row-to-Row Spacing	4.2 mm[.165 in]
Connector Width	9.75 mm[.384 in]



PCB Thickness (Recommended)	1.78 mm[.07 in]
Connector Height	12.8 mm[.504 in]
Connector Length	18 mm[.709 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	255
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as




EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2825261-6 16P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 1586040-8 8P VAL-U-LOK VRT HDR W/P V0	 TE Part # 1-2825261-0 10P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 2825261-6 6P VAL-U-LOK HCS VRT HDR W/P V0
 TE Part # 2825261-2 2P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 2825261-4 4P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 2-2825261-0 20P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 2-2825261-4 24P VAL-U-LOK HCS VRT HDR W/P V0
 TE Part # 2-2825261-2 22P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 1-2825261-4 14P VAL-U-LOK HCS VRT HDR W/P V0	 TE Part # 1-2825261-2 12P VAL-U-LOK HCS VRT HDR W/P V0	

Customers Also Bought

 TE Part #1-1462051-6 HF3 52 = 50OHM 140MW 4.5V MONO	 TE Part #1888617-1 Cage Assy, QSFP, Through Bezel	 TE Part #9-1879337-4 CPF 0603 23K2 1% 50PPM 1K RL	 TE Part #5787443-1 HDR ASY,RA,NO KEY,RET TAIL
--	---	--	--



TE Part #1586041-6
6P VAL-U-LOK R/A HDR V2



TE Part #292228-6
1.5 MINI CT SGL H SMT W/O BOSS



TE Part #5175472-1
CHAMP 050 BTB PLUG H W/LEG 20P



TE Part #1-1734775-1
Std USB Type A, Flag, T/H, 1.8A



TE Part #292228-4
1.5 MINI CT SGL H SMT W/O BOSS



TE Part #2176325-7
CRGP 0402 33R 1%

Documents

Product Drawings

8P VAL-U-LOK HCS VRT HDR W/P V0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2825261-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2825261-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2825261-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English