



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0603

Power Rating: .063 W

Surface Mount Resistor Termination Type: Solder

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Power Rating	.063 W

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	45 mm[1.17 in]
Product Length	320 mm[12.6 in]
Product Width	260 mm[10.24 in]

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1614758-2
RN 0603 4R75-97R6 LAB KIT



TE Part # 1614758-9
RN 0402 1K0-15K LAB KIT



TE Part # 1614758-7
RN 0805 10K2-511K LAB KIT



TE Part # 1614758-4
RN 0603 10K2-332K LAB KIT



TE Part # 1614758-6
RN 0805 100R-10K LAB KIT



TE Part # 1614758-8
RN 0402 51R1-976R LAB KIT



TE Part # 1614758-5
RN 0805 4R75-97R6 LAB KIT



Also in the Series | [Holsworthy RN73](#)

Surface Mount Resistors(3641)

Customers Also Bought

TE Part #1467939-1
[031-0024-0001](#)

TE Part #2170708-1
[CAGE ASSY, 1X6, QSFP28, SPRING, HS, LP](#)

TE Part #9-1879127-7
[RN 0402 536R 0.1% 10PPM CUT LENGTH](#)

TE Part #2-84533-6
[1.25MM FFC POST PLATED H 26P](#)

TE Part #EF9974-000
[202K132-25L/225-0](#)

TE Part #1614758-2
[RN 0603 4R75-97R6 LAB KIT](#)

TE Part #325802
[TERMINAL,AMPOWER 300MCM 5/16](#)

TE Part #1614758-4
[RN 0603 10K2-332K LAB KIT](#)

TE Part #1-1627134-3
[H2833ET/R1800](#)

Documents

- [CAD Files](#)
- [3D PDF](#)
- 3D
- Customer View Model
- [ENG_CVM_CVM_1614758-3_BA.2d_dxf.zip](#)
- English
- Customer View Model



[ENG_CVM_CVM_1614758-3_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1614758-3_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English