



Product data sheet

Power tools for trade & industry

Cordless Impact Driver

PRO GDR 18V-215



Your Go-To tool for fast and accurate screwdriving

The most important data

Battery voltage	18.0 V
Torque, max.	215 Nm
No-load speed	0-2,100 rpm

Order number 0 601 9N2 020

Technical data

Additional data

Battery voltage	18.0 V
Torque, max.	215 Nm
No-load speed	0-2,100 rpm
Tool holder	1/4" internal hexagon
Weight incl. battery	1.4 kg
No-load speed (1st level)	0-2,100 rpm
No-load speed (2nd level)	0-3,300 rpm
Torque settings	2
Weight excl. battery	1 kg
Impact rate	0-3,800 bpm
Impact rate (1st level)	0-3,000 bpm
Impact rate (2nd level)	0-3,800 bpm
BITURBO	No

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	21.3 m/s ²
Uncertainty K	1.6 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Fast and efficient, also for long screws and hard wood thanks to 3,300 RPM and 215 Nm torque
- Easily handles tight spaces thanks to cordless compact design
- Good quality finish due to two Auto Driving Modes that come with Automatic Shut Down & Automatic Slow Down functions



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/iq/en/wac/>

