



E2E-X5MC1L12 2M

Proximity sensor, inductive, nickel-brass, long body, M12, unshielded, 5 mm, DC, 3-wire, NPN NO, 2 m cable

Specifications

Size	M12
Mounting type	Non-flush
Sensing distance	5 mm
Overall length of sensor	69.1 mm
Thread length	48 mm
Material housing	Brass, nickel plated
Output type	NPN
Operation mode	NO
Connection method	Cable
Cable specifications	PVC (oil-resistant)
Cable length	2 m
IO-Link function	×
IO-Link baud rate	Not Applicable
Degree of protection (IP)	IP67/IP67G/IP69K

Downloads

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q)- XB_XC_basic_model Instruction Sheet

EN PDF 2.28 MB



IO-Link Series Brochure

EN PDF 6.41 MB

