



ORBITAL SANDER 150MM-5NV

RC9361S

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:16





DESCRIPTION

ORBITAL SANDER 150MM-5NV

POWERFUL Its powerful motor (200 W) and high speed make it possible to satisfy every situation encountered. Furthermore, its profile means you have a perfect view of the backing pad making the operator's work easier. Sander made of composite material designed for standard sanding. Variable speed control. Exhaust on silencer.

STANDARDS / DIRECTIVES

2006/42/CE, ISO 11148-6, ISO 15744, ISO 28927-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:16



SPECIFIC DATA

Designation	ORBITAL SANDER 150MM-5NV
Sales reference	RC9361S
L (mm)	260
Weight (g)	1260
l (mm)	150
h (mm)	135
Power (W)	12 000
Rotation speed (rpm)	2,8
Vibration (m/s²)	88
Noise level (dBa)	6,3
C mm	1/4"
C min mm	5
C mm	150
Eccentricity (mm)	
Tray Ø (mm)	M2 SAM Equipment and Machine Guarantee
Guarantee	

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:16

