



Part Number: 9873

Audio, Control & Instrument, #20-3pr, PO, Individ. Foil, PVC Jkt, CM

Product Description

Audio, Control & Instrument Cable, 20 AWG stranded (7x28) tinned copper conductors, polypropylene insulation, twisted pairs, individually shielded with Beldfoil® (100% coverage), 22 AWG stranded tinned copper drain wire, overall PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
20	7x28	TC - Tinned Copper	6	3

Conductor Count:	6
Conductor Size:	20 AWG

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.015 in

Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil® (Z-Fold®)	100 %	TC - Tinned Copper	22	19x34

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.341 in	0.035 in

Construction and Dimensions

Stranding

Lay Direction	Twists
Left Hand	6.9 twist/ft

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
14 Ohm/1000ft	10.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	55 pF/ft

Inductance

Nominal Inductance

0.18 µH/ft

Impedance

Nominal Characteristic Impedance

50 Ohm

Delay

Max. Delay Skew | Nominal Velocity of Propagation (VP) [%]

66 ns/100m | 66 %

Current

Max. Recommended Current [A]

2.7 Amps per conductor @ 25°C A

Current Table Note: 10C Temperature Rise

Voltage

UL Description | UL Voltage Rating

UL type CM | 300 V RMS

UL AWM 2919 | 30 V RMS

Temperature Range

UL Temp Rating: 80°C (UL AWM Style 2919)

Operating Temp Range: -20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight: 57 lbs/1000ft

Max Recommended Pulling Tension: 106 lbs

Min Bend Radius/Minor Axis: 3.5 in

Standards

NEC Articles: 800

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

UL AWM Style: 2919 (30 V 80°C)

CPR Euroclass: Eca

Applicable Environmental and Other Programs

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

EU RoHS Compliance Date (yyyy-mm-dd): 2004-01-01

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Suitability

Suitability - Indoor: Yes

Flammability, LS0H, Toxicity Testing

UL Flammability: UL1685 UL Loading

CSA Flammability: FT1

UL voltage rating: 300 V RMS

Plenum/Non-Plenum

Plenum (Y/N): No

Part Number

Variants

Item # | Color | Footnote

9873 060100 | Chrome |

9873 0601000	Chrome	C
9873 060250	Chrome	C
9873 060500	Chrome	C
9873 0605000	Chrome	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.