

# Safety data sheet

according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

#### · Trade name: 824

· Other Means of Identification: Isopropyl Alcohol: Electronics Cleaner

#### · Related Part Number:

824-Liquid, 824-100ML, 824-500ML, 824-1L, 824-4L, 824-20L, 824-205L, 824-1G, 824-100MLCA, 824-1LCA, 824-1LX6, 824-500MLCA

#### · CAS Number:

67-63-0

#### · EC number:

200-661-7

#### · Index number:

603-117-00-0

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

· Application of the substance / the mixture Electronics cleaner

· Uses advised against Not for use on monitor screens or glass with anti-glare coatings

### 1.3 Details of the supplier of the safety data sheet

#### · Manufacturer/Supplier:

MG Chemicals Ltd. (Head Office)  
1210 Corporate Drive  
Burlington, Ontario L7L 5R6  
CANADA  
+(1) 905-331-1396  
info@mgchemicals.com

MG Chemicals  
Heame House, 23 Bliston Street  
Sedgely Dudley DY3 1JA.  
United Kingdom  
+(44) 1663 362888

MG Chemicals Ltd.  
Level 2, Vision Exchange, Building Territorials Street,  
Zone 1, Central Business, District,  
Birkirkara CBD 1070,  
MALTA

· Further information obtainable from: sds@mgchemicals.com

### 1.4 Emergency telephone number:

Verisk 3E (Access code: 335388)  
+(44) 20 3514787  
+(1) 760 476 3961  
UK Toll free: +(0) 800 680 0425

Members of the public seeking specific information on poisons should contact:

In England and Wales: NHS 111 - dial 111

In Scotland: NHS 24 - dial 111

GB —

(Contd. on page 2)

# Safety data sheet

according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

**Trade name: 824**

(Contd. of page 1)

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008



GHS02 flame

Flam. Liq. 2 H225 Highly flammable liquid and vapour.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

### 2.2 Label elements

#### Labelling according to Regulation (EC) No 1272/2008

The substance is classified and labelled according to the GB CLP regulation.

##### Hazard pictograms



GHS02



GHS07

##### Signal word Danger

##### Hazard-determining components of labelling:

Propan-2-ol

##### Hazard statements

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

##### Precautionary statements

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.

No smoking.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves / eye protection.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P370+P378 In case of fire: Use CO<sub>2</sub>, powder or water spray to extinguish.

P501 Dispose of contents and container in accordance with local, regional, and national regulations.

##### Additional information:

EUH066 Repeated exposure may cause skin dryness or cracking.

### 2.3 Other hazards

#### Results of PBT and vPvB assessment

· PBT: Not applicable.

· vPvB: Not applicable.

#### Determination of endocrine-disrupting properties

Endocrine Disruptor substance ≥ 0.1% = none

GB

(Contd. on page 3)

## Safety data sheet according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

**Trade name: 824**

(Contd. of page 2)

### SECTION 3: Composition/information on ingredients

**· 3.1 Substances****· CAS No. Description**

67-63-0 Propan-2-ol

**· Identification number(s)**

· EC number: 200-661-7

· Index number: 603-117-00-0

**· Dangerous components:**

CAS: 67-63-0	Propan-2-ol	99.7%
EINECS: 200-661-7	Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	
Index number: 603-117-00-0		

### SECTION 4: First aid measures

**· 4.1 Description of first aid measures****· After inhalation:**

Remove person to fresh air and keep comfortable for breathing.  
If feeling unwell: Call a POISON CENTRE or doctor.

**· After skin contact:**

Take off immediately all contaminated clothing.  
Wash with plenty of soap and water.

**· After eye contact:**

Rinse cautiously with water for 20 minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

If eye irritation persists: Get medical advice or attention.

**· After swallowing:**

Rinse mouth.  
Do NOT induce vomiting.  
If symptoms persist consult doctor.

**· 4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

**· 4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

### SECTION 5: Firefighting measures

**· 5.1 Extinguishing media****· Suitable extinguishing agents:**

CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

**· 5.2 Special hazards arising from the substance or mixture**

Vapors are heavier than air. Vapors may travel to sources of ignition near the ground. They can cause flash fire or ignite explosively.

Prevent fire-fighting wash from entering waterway or sewer system.

**· Hazardous combustion products:** Carbon Oxides (CO<sub>x</sub>)

(Contd. on page 4)

GB

## Safety data sheet according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

**Trade name: 824**

(Contd. of page 3)

**· 5.3 Advice for firefighters**

- **Protective equipment:** Wear self-contained breathing apparatus and full fire-fighting turn-out gear.

**SECTION 6: Accidental release measures****· 6.1 Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation

Remove or keep away all sources of extreme heat or open flames.

Avoid breathing mist, spray, or vapors.

**· 6.2 Environmental precautions:**

Dilute with plenty of water.

Do not allow to enter sewers/ surface or ground water.

**· 6.3 Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Collect liquid in a sealable, chemical-resistant container.

Wash residue with a paper towel and place dirty towels in container.

Use soap and water to remove the last traces of residue.

**· 6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

**SECTION 7: Handling and storage****· 7.1 Precautions for safe handling**

Wear protective gloves and eye protection.

Wash hands and exposed skin thoroughly after handling.

Take off contaminated clothing and wash it before reuse.

Avoid breathing mist, spray, or vapors.

Use only outdoors or in a well-ventilated area.

**· Information about fire - and explosion protection:**

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Use explosion-proof apparatus / fittings and spark-proof tools.

Ground and bond container and receiving equipment.

**· 7.2 Conditions for safe storage, including any incompatibilities****· Storage:****· Requirements to be met by storerooms and receptacles:**

Store in a cool location.

Keep in a dry and clean area, away from incompatible substances

**· Information about storage in one common storage facility:** Not required.**· Further information about storage conditions:**

Keep container tightly sealed.

Store in cool, dry conditions in well sealed receptacles.

Store locked up.

**· 7.3 Specific end use(s)** See section 1.2

GB —

(Contd. on page 5)

## Safety data sheet according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

**Trade name: 824**

(Contd. of page 4)

### SECTION 8: Exposure controls/personal protection

#### · 8.1 Control parameters

##### · Ingredients with limit values that require monitoring at the workplace:

67-63-0 Propan-2-ol	
WEL	Short-term value: 1250 mg/m <sup>3</sup> , 500 ppm Long-term value: 999 mg/m <sup>3</sup> , 400 ppm

##### · Additional information:

The lists valid during the making were used as basis.

Refer to the national or regional occupational exposure limit regulation for abbreviations and acronyms.

#### · 8.2 Exposure controls

##### · Appropriate engineering controls

No further data; see section 7.

##### · Individual protection measures, such as personal protective equipment

###### · General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

###### · Respiratory protection:

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

Advice should be sought from respiratory protection specialists.

If the product is heated or worker has a known allergic reaction, consider using a full mask with organic vapor cartridge or with an independent air supply.

###### · Hand protection

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.



Protective gloves: EN374

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

###### · Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

###### · Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

###### · Eye/face protection



Safety glasses or tightly sealed goggles: EN 166

### SECTION 9: Physical and chemical properties

#### · 9.1 Information on basic physical and chemical properties

##### · Physical state

Liquid

##### · Form:

Low viscosity

(Contd. on page 6)

GB

# Safety data sheet

according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

## Trade name: 824

(Contd. of page 5)

· Colour:	Colourless
· Odour:	Alcohol-like
· Odour threshold:	0.44 ppm
· Melting point/freezing point:	-88 °C
· Boiling point or initial boiling point and boiling range	≥81.8 °C
· Flammability	Highly flammable.
· Lower and upper explosion limit	
· Lower:	2 Vol % (67-63-0 Propan-2-ol)
· Upper:	12 Vol % (67-63-0 Propan-2-ol)
· Flash point:	12 °C (67-63-0 Propan-2-ol)
· Auto-ignition temperature:	425 °C (67-63-0 Propan-2-ol)
· Decomposition temperature:	Not determined.
· pH	Not determined.
· Viscosity:	
· Kinematic viscosity	Not determined.
· Dynamic at 20 °C:	2.43 mPas
· Solubility	
· water:	Fully miscible.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure at 20 °C:	43 hPa (67-63-0 Propan-2-ol)
· Relative density at 25 °C:	0.785
· Vapour density (air=1):	2.1
· Particle characteristics	Not applicable.
<b>· 9.2 Other information</b>	
· 9.2.1 Information with regard to physical hazard classes	
· Flammable liquids	Highly flammable liquid and vapour.
· 9.2.2 Other safety characteristics	
· Evaporation rate	1.5 (ButAc=1)
· Ignition temperature:	Not determined.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Solvent content:	
· Organic solvents:	99.70 %
· VOC (EC)	99.70 %
· Solids content:	0.3 %
· Molecular weight	60 g/mol

## SECTION 10: Stability and reactivity

- **10.1 Reactivity** At elevated temperatures, may react with aluminum and generate hydrogen gas.
- **10.2 Chemical stability** Chemically stable at normal temperatures and pressures.
  - **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid**  
Avoid open flames, excessive heat, sparks, ignition sources, and incompatible substances.

(Contd. on page 7)  
GB

# Safety data sheet

according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

**Trade name: 824**

(Contd. of page 6)

**10.5 Incompatible materials:**

Strong oxidizing agents  
Strong acids  
Strong bases  
Halogenated compounds  
Aluminum at temperatures ≥49 °C

**10.6 Hazardous decomposition products:**

No dangerous decomposition products known.  
Hazardous combustion products: see section 5.

## SECTION 11: Toxicological information

**11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**

· **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

67-63-0 Propan-2-ol		
Oral	LD50	5,045 mg/kg (rat)
Dermal	LD50	12,800 mg/kg (rabbit)
Inhalative	LC50/4 h	30 mg/L (rat)

· **Primary irritant effect:**

· **Skin corrosion/irritation** Based on available data, the classification criteria are not met.  
· **Serious eye damage/irritation** Causes serious eye irritation.

· **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.

· **Germ cell mutagenicity** Based on available data, the classification criteria are not met.

· **Carcinogenicity** Based on available data, the classification criteria are not met.

· **Reproductive toxicity** Based on available data, the classification criteria are not met.

· **STOT-single exposure** May cause drowsiness or dizziness.

· **STOT-repeated exposure** Based on available data, the classification criteria are not met.

· **Aspiration hazard** Based on available data, the classification criteria are not met.

· **Summary of Effects and Symptoms by Routes of Exposure**

· **Eyes:**

pain  
redness, serious irritation  
tearing of the eyes

· **Skin:**

redness, may cause mild irritation  
dry skin

· **Inhalation:**

headache  
narcotic effects  
weakness  
dizziness or drowsiness

· **Swallowed:** see inhalation symptoms

· **Additional toxicological information:**

· **Delayed and immediate effects as well as chronic effects from short and long-term exposure**

Prolonged or repeated exposure may defat skin and cause skin dryness and cracking, and local redness and discomfort.

(Contd. on page 8)

GB

## Safety data sheet according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

### Trade name: 824

(Contd. of page 7)

#### · 11.2 Information on other hazards

##### · Endocrine disrupting properties

Substance is not listed.

## SECTION 12: Ecological information

#### · 12.1 Toxicity

##### · Aquatic toxicity:

67-63-0 Propan-2-ol

EC50/ 24 h 5,102 mg/L (daphnia)

EC50/ 72 h &gt;2,000 mg/L (algae)

LC50 96h 9,640 mg/L (minnow)

· 12.2 Persistence and degradability No further relevant information available.

· 12.3 Bioaccumulative potential No further relevant information available.

· 12.4 Mobility in soil No further relevant information available.

#### · 12.5 Results of PBT and vPvB assessment

· PBT: Not applicable.

· vPvB: Not applicable.

#### · 12.6 Endocrine disrupting properties

The product does not contain substances with endocrine disrupting properties.

#### · 12.7 Other adverse effects

##### · Additional ecological information:

###### · General notes:

Water hazard class 1 (German Regulation) (Assessment by list): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

## SECTION 13: Disposal considerations

#### · 13.1 Waste treatment methods

· Recommendation This material and its container must be disposed of as hazardous waste.

##### · European waste catalogue

HP3	Flammable
HP4	Irritant - skin irritation and eye damage
HP5	Specific Target Organ Toxicity (STOT)/Aspiration Toxicity

##### · Uncleaned packaging:

###### · Recommendation:

Containers may still present a chemical hazard/ danger when empty.

Dispose of contents in accordance with all local, regional, national, and international regulations.

Where possible retain label warnings and SDS and observe all notices pertaining to the product.

(Contd. on page 9)

— GB —

# Safety data sheet

according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

## Trade name: 824

(Contd. of page 8)

- Recommended cleansing agents: Water, if necessary together with cleansing agents.

## SECTION 14: Transport information

· 14.1 UN number or ID number	· ADR, IMDG, IATA	UN1219
· 14.2 UN proper shipping name	· ADR, IMDG	ISOPROPANOL (ISOPROPYL ALCOHOL)
	· IATA	Isopropanol (isopropyl alcohol)
<b>· 14.3 Transport hazard class(es)</b>		
· ADR, IMDG, IATA		
		
· Class	3	Flammable liquids.
· Label	3	
· 14.4 Packing group	· ADR, IMDG, IATA	II
· 14.5 Environmental hazards:		Not applicable.
· 14.6 Special precautions for user		Not applicable.
· Hazard identification number (Kemler code):	33	
· EMS Number:	F-E,S-D	
· Stowage Category	B	
· 14.7 Maritime transport in bulk according to IMO instruments		Not applicable.
<b>· Transport/Additional information:</b>		
	Limited Quantity	
824-100ML, 824-100MLCA, 824-500ML, 824-500MLCA, 824-1L, 824-1IX6, 824-1LCA		
· ADR		
· Limited quantities (LQ)	1L	
· Excepted quantities (EQ)	Code: E2	
	Maximum net quantity per inner packaging: 30 ml	
	Maximum net quantity per outer packaging: 500 ml	
· Transport category	2	
· Tunnel restriction code	D/E	
· IMDG		
· Limited quantities (LQ)	1L	
· Excepted quantities (EQ)	Code: E2	
	Maximum net quantity per inner packaging: 30 ml	

(Contd. on page 10)

— GB —

## Safety data sheet according to UK REACH

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

### Trade name: 824

(Contd. of page 9)

· Maximum net quantity per outer packaging: 500 ml
· UN "Model Regulation": UN 1219 ISOPROPANOL (ISOPROPYL ALCOHOL), 3, II

## SECTION 15: Regulatory information

### · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### · Poisons Act

##### · Regulated explosives precursors (Part 1)

Substance is not listed.

##### · Regulated poisons (Part 2)

Substance is not listed.

##### · Reportable explosives precursors (Part 3)

Substance is not listed.

##### · Reportable poisons (Part 4)

Substance is not listed.

#### · Directive 2012/18/EU

##### · Named dangerous substances - ANNEX I Substance is not listed.

##### · Seveso category P5c FLAMMABLE LIQUIDS

##### · Qualifying quantity (tonnes) for the application of lower-tier requirements 5,000 t

##### · Qualifying quantity (tonnes) for the application of upper-tier requirements 50,000 t

#### · REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3

#### · DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

Substance is not listed.

### · 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

## SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

#### · Relevant phrases

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

#### · Department issuing SDS: Regulatory department

#### · Contact: sds@mgchemicals.com

#### · Date of previous version: 03.06.2024

#### · Version number of previous version: 7.00

#### · Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

(Contd. on page 11)

GB

**Safety data sheet**  
*according to UK REACH*

Printing date 25.10.2024

Version number 7.01 (replaces version 7.00)

Revision: 25.10.2024

**Trade name: 824**

(Contd. of page 10)

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Liq. 2: Flammable liquids – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

GB —