

Product datasheet

Specifications



RISER DISTRIBUTION LENGTH 2M 3O 1000A

KSA1000EV4203

EAN Code: 3606480003875

Main

Range	Canalis
Device short name	KSA
Offer type	Rising main
Product or component type	Busbar trunking
Busbar description	Vertical distribution length
Product compatibility	Canalis KSA busbar trunking 500...1000 A
Conductors material	Aluminium
Busbar trunking polarity	3L + N + PE
Number of tap-off outlets	3
[Ie] rated operational current	1000 A at 35 °C
IP degree of protection	IP55 conforming to IEC 60529
Mounting mode	By screws
Dimension type	Fix
Length	2 m
Colour	White (RAL 9001)

Complementary

Number of poles	4
Neutral position	Right
Mounting position	Vertical
[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	690 V
[Icw] rated short-time withstand current	37.4 kA
[Ipk] rated peak withstand current	78.7 kA
Electrical connection	Lubricated sliding contact
Width	113 mm
Height	146 mm
Net weight	36.5 kg
Tap-off unit interval	500 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Radiated magnetic field	1.27 µT
Thermal stress limit	1758000 kA².s
THDI	0...15 % 1000 A 15...33 % 800 A 33...100 % 630 A
Maximum voltage drop	<0.005 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.007 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.007 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.008 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Standards	IEC 61439-1 IEC 61439-6

Environment

IK degree of protection	IK08 conforming to IEC 62262
Ambient air temperature for operation	35 °C (without derating) 55 °C (with derating factor)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.2 cm
Package 1 Width	16.8 cm
Package 1 Length	213.8 cm
Package 1 Weight	42.02 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
Halogen-free status	Halogen free product
PVC free	Yes
Silicone-free	Yes

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins