


Geberit Mapress Copper T-piece, equal



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water $\leq 120\text{ }^{\circ}\text{C}$
- For service water and process water
- For compressed air (oil purity class 0–3)

- For negative pressure
- For inert gases (e.g. nitrogen)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed up to $\varnothing \leq 54\text{ mm}$

- Seal ring made of CIIR, black, up to $\varnothing \leq 54\text{ mm}$
- Seal ring made of EPDM, black, from $\varnothing > 54\text{ mm}$
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material	Cu-DHP copper CW024A (EN 1412)
------------------	--------------------------------

Art. no.	DN	d, $\varnothing$ mm	arc $^{\circ}$	L cm	L1 cm	I cm	Z cm	Z1 cm
61000	10	12	90	6.2	3.1	3.1	1.4	1.4
61002	12	15	90	6.4	3.1	3.2	1.2	1.2
61003	15	18	90	6.8	3.4	3.4	1.4	1.4
61004	20	22	90	7.4	3.7	3.7	1.6	1.6
61005	25	28	90	8.4	4.2	4.2	1.9	1.9

Art. no.	DN	d, ø mm	arc °	L cm	L1 cm	I cm	Z cm	Z1 cm
61006	32	35	90	10	5.9	5	2.4	3.3
61007	40	42	90	11.4	6.6	5.7	2.7	3.6
61008	50	54	90	13.8	7.8	6.9	3.4	4.3
61010	65	66.7	90	22	10.5	11	6	5.5
61011	65	76.1	90	23	11	11.5	6.2	5.7
61012	80	88.9	90	26	12.7	13	7	6.7
61013	100	108	90	31	15.3	15.5	8	7.8