



Main

Range	Acti9
Product name	Acti9 iLG40
Product or component type	Residual current circuit breaker (RCCB)
Device short name	IIG40
Poles description	3P + N
Neutral position	Left
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Quality labels	NF

Complementary

Device location in system	Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	380...415 V AC 50 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 1500 A
Rated conditional short-circuit current	10000 A
[Ui] rated insulation voltage	500 V AC 50 Hz
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	74 mm
Net weight	345 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	15000 cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminals bottom 1...35 mm² rigid Tunnel type terminals bottom 1...25 mm² flexible Tunnel type terminals top 1...16 mm² rigid Tunnel type terminals top 1...10 mm² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.M bottom 2 N.m top

Environment

Standards	EN/IEC 61008-2-1
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61008-2-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product