


FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and long-lasting performance
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and enhances cable longevity
- **4 Cores with 24/0.2 Strands:** Ensures flexibility and ease of installation in tight spaces
- **Operating Temperature Range -15 °C to 90 °C:** Suitable for a wide range of environments
- **Voltage Rating of 500 V:** Supports high voltage applications safely
- **Plain Conductor Type:** Simplifies termination and connection processes
- **White Jacket Colour:** Facilitates easy identification and organisation

RS PRO 0.75 mm² Flexible Cable, 50 m

RS Stock No: 606-118



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations requiring flexibility and robustness, making it ideal for dynamic environments.

General Specifications

| | |
|--------------------|-----------------|
| Conductor Material | Annealed Copper |
| Conductor Type | Plain |
| Jacket Colour | White |
| Product Type | Flexible Cable |

Mechanical Specifications

| | |
|------------------|----------------------|
| Cable CSA | 0.75 mm ² |
| Cable Length | 50 m |
| Core Strands | 24/0.2 |
| Jacket Material | Polyvinyl Chloride |
| Number of Cores | 4 |
| Outside Diameter | 8.3 mm |

Operation Environment Specifications

| | |
|-------------------------------|--------|
| Maximum Operating Temperature | 90 °C |
| Minimum Operating Temperature | -15 °C |

Approvals

| | |
|---------------------|---|
| Standards/Approvals | ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228 |
|---------------------|---|

Electrical Specifications

| | |
|---------|-------|
| Voltage | 500 V |
|---------|-------|