

8BCM0005.15250-0

1 General information

- Can be used in cable drag chains
- Extension cable for 8BCMxxxx.1523A-0 / 8ECMxxxx.1523C-0
- speedtec - Innovative connector system for secure connections

2 Order data

Order number	Short description	Figure
8BCM0005.15250-0	Motor cables 10 mm² Cable extension for 10 mm ² motor cables with speedtec/standard connector size 1.5, length 5 m, can be used in cable drag chains	

Table 1: 8BCM0005.15250-0 - Order data

3 Technical data

Order number	8BCM0005.15250-0
General information	
Cable cross section	4x 10 mm ² + (2x 0.75 mm ²)C + (2x 1.5 mm ²)C
Durability	Oil resistance per HD 22.10 appendix A DIN EN 60811-404 ¹⁾
Certification	UL AWM style 20234, 80°C, 1000 V, E63216 and CSA AWM I/II A/B, 90°C, 1000 V, FT2 LL46064
Certifications	
CE	Yes
UKCA	Yes
UL	cULus E225616
EAC	Power conversion equipment
	Yes
Cable construction	
Power lines	
Quantity	4
Wire insulation	PP
Wire colors	Black, brown, blue, yellow/green
Variant	Tinned copper stranded wire
Cross section	10 mm ²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	PP
Wire colors	White, white/red, white/blue, white/green
Variant	Tinned copper stranded wire
Cross section	2x 0.75 mm ² + 2x 1.5 mm ²
Shield	Individually shielded in pairs, tinned copper braiding, optical coverage >85% and foil shield
Stranding	White with white/red and white/blue with white/green
Cable stranding	With filler elements and foil shield
Cable shield	Tinned copper braiding, optical coverage >85% and foil shield
Outer jacket	
Material	TPU
Color	Orange, similar to RAL 2003 flat
Labeling	BERNECKER + RAINER 4x10,0+2x2x1,5 FLEX UL AWM STYLE 20234 80°C 1000 V E63216 CSA AWM I/II A/B 90°C 1000 V FT2 LL46064
Connector	
Type	8-pin female speedtec motor connector, size 1.5
Mating cycles	<500
Contacts	8 (4 power and 4 signal contacts)
Additional connectors	8-pin male coupling Mating cycles: <500 Contacts: 8
Degree of protection per EN 60529	Degree of protection per EN 60529: IP66/67 when connected IP66/67 when connected

Table 2: 8BCM0005.15250-0 - Technical data

Order number	8BCM0005.15250-0
Electrical properties ¹⁾	
Operating voltage	Max. 1000 VAC (UL)
Test voltage	
Wire - Wire	4 kV
Wire - Shield	4 kV
Conductor resistance	
Power lines	≤2 Ω/km
Signal line	0.75 mm ² : ≤26.7 Ω/km, 1.5 mm ² : ≤13.7 Ω/km
Insulation resistance	≥500 MΩ*km
Current-carrying capacity per DIN VDE 0298 part 4, table 11	
Wall mounting	64.6 A
Installed in conduit or cable duct	54.6 A
Installed in cable tray	68.3 A
Ambient conditions ¹⁾	
Temperature	
Moving	-20°C to +80°C
Static	-20°C to +90°C
Mechanical properties ¹⁾	
Dimensions	
Length	5 m
Diameter	20.1 mm ±0.4 mm
Bend radius	
Single bend	>62 mm
Moving	>154 mm
Drag chain data	
Acceleration	Max. 50 m/s ² (depends on the length of the travel path)
Flex cycles ²⁾	≥5,000,000
Velocity	Max. 300 m/min
Weight	2.7 kg

Table 2: 8BCM0005.15250-0 - Technical data

- 1) Values refer to the raw cable being used.
2) At an ambient temperature from -20°C to +60°C.

4 Wiring

4.1 Cable construction

Construction


		
Pos.	Description	Note
1	Motor line	4x 10 mm ² + 2x 0.75 mm ² + 2x 1.5 mm ²
2	8-pin female circular connector	
3	8-pin male coupling	

Table 3: 10 mm² motor cables - Cable construction

4.2 Pinout



Circular connector	Pin	Description	Function	Coupling
	U	U	Motor connection U	
	Ground symbol	PE	Protective ground conductor	
	W	W	Motor connection W	
	V	V	Motor connection V	
	1	T+	Temperature +	
	2	T-	Temperature -	
	+	B+	Brake +	
	-	B-	Brake -	

Table 4: Pinout

4.3 Cable diagram




Figure 1: 8BCMxxxx.15250-0 - Cable diagram