


Product description **M12 Female cable connector, Contacts: 4, unshielded, moulded on the cable, IP69K, UL 2238, PUR, black, 4 x 0.34 mm<sup>2</sup>, with LED PNP closer, 5 m**

Area **M12-A**  
Coding **A-coded**  
Series **763**  
Part no. **77 3630 0000 50004-0500**


### Illustration




### Pin assignment plans



### Scale drawing



### Contact arrangement (Plug-in side) Cable length tolerance



cable length	tolerance
≥ 0,10 m	+ 0,03 m
≥ 0,20 m	+ 0,04 m
≥ 0,50 m	+ 0,07 m
≥ 1,00 m	+ 0,10 m
≥ 2,00 m	+ 0,15 m
≥ 5,00 m	+ 0,20 m
≥ 10,0 m	+ 0,25 m
≥ 20,0 m	+ 0,35 m

### Technical data

#### General features

Part no.	<b>77 3630 0000 50004-0500</b>
Connector design	Female cable connector
Type standard	DIN EN 61076-2-101
Coding	A-coded
Cable length	5 m (Standard 2 m and 5 m. Other lengths are available on request.)
Version	Connector socket straight
Connector locking system	screw
Termination	moulded on the cable
Degree of protection	IP69K
Connection cross-section	0.34 mm <sup>2</sup> / AWG 22
Temperature range from/to	-25 °C / 90 °C

Product description	<b>M12 Female cable connector, Contacts: 4, unshielded, moulded on the cable, IP69K, UL 2238, PUR, black, 4 x 0.34 mm<sup>2</sup>, with LED PNP closer, 5 m</b>
Area	<b>M12-A</b>
Coding	<b>A-coded</b>
Series	<b>763</b>
Part no.	<b>77 3630 0000 50004-0500</b>

Mechanical operation	> 100 Mating cycles
Weight (g)	220.05
Customs tariff number	85444290
Country of Origin	DE

### Electrical parameters

Rated voltage	10 - 30 V
Rated impulse voltage	500 V
Rated current	4.0 A
Insulation resistance	$\geq 10^{10} \Omega$
Pollution degree	3
Overvoltage category	II
Insulating material group	II
EMC compliance	unshielded

### Material

Housing material	PUR
Contact body material	PUR
Contact material	CuSn (bronze)
Contact plating	Au (gold)
Locking material	Zinc die-cast nickel-plated
REACH SVHC	None (No pollutants)
SCIP number	SCIP-number not available

### Cable data - Structure of the cable

Cable diameter	4.7 mm
Cross section	4 x 0.34 mm <sup>2</sup>
Sheath material	PUR
Single-lead insulation	PP9Y halogen-free
Single-lead structure	43 x 0.10 mm
Cable color	black

### Cable data - Electrical properties

Conductor resistance	60 $\Omega$ /Km (20°C)
----------------------	------------------------

### Cable data - Mechanical properties

Bending radius, fixed cable	$\geq 5 \times \emptyset$
Bending radius, moving cable	$\geq 10 \times \emptyset$
Bending cycles	> 5 million
Permitted acceleration	$\geq 5 \text{ m/s}^2$
Travel distance, horizontal	$\geq 5 \text{ m}$
Travel distance, vertical	$\geq 5 \text{ m}$
Travel speed	$\leq 200 \text{ m/min}$

Product description	<b>M12 Female cable connector, Contacts: 4, unshielded, moulded on the cable, IP69K, UL 2238, PUR, black, 4 x 0.34 mm<sup>2</sup>, with LED PNP closer, 5 m</b>
Area	<b>M12-A</b>
Coding	<b>A-coded</b>
Series	<b>763</b>
Part no.	<b>77 3630 0000 50004-0500</b>

#### Cable data - Thermal properties

Temperature range cable in move from/to	-25 °C / 80 °C
Temperature range cable fixed from/to	-50 °C / 80 °C

#### Cable data - Other features

Halogen free	yes
--------------	-----

#### Authorization/approvals

Approvals	UL 2238
-----------	---------

#### Classifications

eCl@ss 11.1	27-06-03-11
ETIM 9.0	EC002638

#### Declarations of conformity

RoHS Directive	2011/65/EU (EN 50581:2012)
----------------	----------------------------

Product description	<b>M12 Female cable connector, Contacts: 4, unshielded, moulded on the cable, IP69K, UL 2238, PUR, black, 4 x 0.34 mm<sup>2</sup>, with LED PNP closer, 5 m</b>
Area	<b>M12-A</b>
Coding	<b>A-coded</b>
Series	<b>763</b>
Part no.	<b>77 3630 0000 50004-0500</b>

## General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).

The protection class specification applies on condition that the four mounting holes are made as blind holes.