

Back-of-Panel Components

Contact Blocks with Latch — Composite

800F – P X 0 1 E
 a b c d e



a

Style	
Code	Description
P	Plastic latch
M	Metal latch

b

Contact Block(s) Termination Style*	
Code	Description
X	Screw termination
Q	Spring-clamp termination

* Six circuits maximum allowable.

c

N.O. (Normally Open) Circuits	
Code	Description
0	No contact
1	1 N.O.
2	2 N.O.
3	3 N.O.
4	4 N.O.
5	5 N.O.
6	6 N.O.

d

N.C. (Normally Closed) Circuits	
Code	Description
0	No contact
1	1 N.C.
2	2 N.C.
3	3 N.C.
4	4 N.C.
5	5 N.C.
6	6 N.C.

e

Specialty Contact Block(s)	
Code	Description
Blank	Standard blocks
V	Low voltage — QuadCONNECT™
E	N.O. early make
L	N.C. late break
B	N.C. early break
S	N.C. self-monitoring

Power Modules with Latch — Composite

800F – M N 3 G
 a b c d



a

Style	
Code	Description
P	Plastic latch
M	Metal latch

b

Power Module Type§*	
Code	Description
D	Incandescent module, screw termination
N	Integrated LED module, screw termination
Q	Integrated LED module, spring-clamp termination

c

Voltage	
Code	Description
0	No bulb△
1	6V AC/DC△
2	12V AC/DC△
3	24V AC/DC
4	48V AC/DC△
5	120V AC
7	240V AC*

d

Lamp Color▲	
Code	Description
C	Incandescent
R	Red LED
G	Green LED
W	White LED

§ LED modules for use with all illuminated operators. Incandescent module for use with pilot lights, momentary push buttons, and momentary mushroom operators only.

* Four circuits maximum allowable when power module is used. Contact blocks cannot be stacked on power module.

△ Only available for incandescent module.

▲ Only available for integrated LED module.

▲ For best illumination results, LED color should match lens color. For yellow operator, select a white LED.

Back-of-Panel Components, Continued

Power Modules with Contact Blocks and Latch — Composite

800F – P N 5 R X 1 0 E
 a b c d e f g h

a

Style	
Code	Description
P	Plastic latch
M	Metal latch

b

Power Module Type*‡	
Code	Description
D	Incandescent module, screw termination
N	Integrated LED module, screw termination
Q	Integrated LED module, spring-clamp termination

c

Voltage	
Code	Description
0	No bulb§
1	6V AC/DC§
2	12V AC/DC§
3	24V AC/DC
4	48V AC/DC§
5	120V AC
7	240V AC*

d

Lamp Color▲	
Code	Description
C	Incandescent
R	Red LED
G	Green LED
W	White LED

e

Contact Block(s) Termination Style	
Code	Description
X	Screw termination
Q	Spring-clamp termination

f

N.O. (Normally Open) Circuits	
Code	Description
0	No contact
1	1 N.O.
2	2 N.O.
3	3 N.O.
4	4 N.O.

g

N.C. (Normally Closed) Circuits	
Code	Description
0	No contact
1	1 N.C.
2	2 N.C.
3	3 N.C.
4	4 N.C.

h

Specialty Contact Block(s)	
Code	Description
Blank	Standard blocks
V	Low voltage — QuadCONNECT™
E	N.O. early make
L	N.C. late break
B	N.C. early break
S	N.C. self-monitoring

* Four circuits maximum allowable when power module is used. Contact blocks cannot be stacked on power module.

‡ LED modules for use with all illuminated operators. Incandescent module for use with pilot lights, push buttons, and momentary mushroom operators only.

§ Only available for incandescent module.

▲ Only available for integrated LED module.

▲ For best illumination results, LED should match lens color. For yellow operator, select a white LED.

