

## Linear ball bearing and housing units

### KGBAO40-PP-AS (Series KGBAO..-PP-AS)

open design, sealed, greased, with relubrication facility;  
corrosion-resistant design possible

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	40 mm	
H	82,5 mm	
B	108 mm	
L	80 mm	Tolerance: h12
	5	Number of rows of balls
1)		Main load direction
A3	18 mm	
A5	54 mm	Tolerance: +/-0,015
B2	18,2 mm	Dimension B2 on diameter Fw
H2	45 mm	Tolerance: +/-0,01
H6	11 mm	Tolerance: 0/-0,5

JB	86 mm	Tolerance: +/-0,2
JL	58 mm	Tolerance: +/-0,2
K5	M8	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
K8	NIPA2	Lubrication nipple
L4	78 mm	
L5	56 mm	
N1	9,2 mm	
N3	15 mm	
W1	4 mm	Note maximum tightening torque. Tightening torque max. 5 Nm
$\alpha$	54 °	
m	1,07 kg	Mass
C	6100 N	Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.
C <sub>0</sub>	4600 N	Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.

