

Features

- Especially suitable for plant construction, logistics and general industrial requirements
- For universal audible applications
- Well-designed electromechanical horn combined with LED flashing beacon
- Amber flashing beacon
- Typical horn tone 88dB
- 230-240V AC operation

RS PRO Sounder / Beacon

RS Article.: 0658302



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Aesthetically designed electromechanical alarm horn that is used in various industries.
- No need to buy two separate products. This signal horn gives a tough, high-quality option for visual and audible signalling.
- Combination of an electromechanical cone shaped horn with a flashing LED beacon emitting light at equal intervals, creating 2 blinking light flashes every second.
- A steady high-volume tone of 88dB provided with a very strong flashing amber light for perfect warning signals.
- Sound and light separately switchable with an IP43 degree of protection suitable for 230-240V AC supply voltage requirements
- Easily mounted onto a wall via 2 screws with cable entry to the rear

General Specifications

Housing	ABS grey (RAL 7035)
Type of Mounting	Any. Sound outlet opening at bottom
Fitting	2 bolts / screws
Magnetic Type	No
Lens Colour	Amber (ribbed inside)
Lamp Included	Yes
Tone	Steady Tone
Beacon Type	LED Flashing Beacon
Flash Frequency	2Hz
Duty Cycle	100%

Mechanical Specifications

Dimensions	75mm (w) x 80mm (d) x 213mm (h)
Mounting Style	Screw Mount
Weight	225g

Electrical Specifications

Supply Voltage	230-240 VAC, 50Hz
Volume	88dB
Current Type	AC
Current Consumption	40mA

Protection Category

IP Rating	IP43
-----------	------

Operation Environmental Specifications

Maximum Temperature	+50°C
Minimum Temperature	-20°C

Approvals

Compliance/Certifications	CE
Declarations	RoHS Compliant / REACH

