



Product designation				Changeover Switch
Product type designation				GLC UL
Number of poles		Nr.	4	
Operating voltage type			AC	
<b>Contact characteristics</b>				
IEC Conventional free air thermal current $I_{th} \leq 40^\circ\text{C}$		A	400	
Rated insulation voltage $U_i$ IEC/EN		V	1000	
Rated impulse withstand voltage $U_{imp}$		kV	12	
Operating current $I_e$				
	AC-31B			
		400V	A	400
		500V	A	400
		690V	A	400
	AC-32B			
		400V	A	400
		500V	A	400
		690V	A	400
	AC-33B			
		400V	A	400
		500V	A	400
		690V	A	400
Power dissipation per pole max			W	26.0
Rated operational power AC23A				
		400V	kW	200
		690V	kW	400
Rated short time current (1s) $I_{cw}$ (rms)			kA	12.5
Rated short time current (0.3s) $I_{cw}$ (rms)			kA	20
Conditional short-circuit current (rms)			kA	80
Short-circuit protection with fuse			Class/A	J/400
Making capacity AC23A 400V			A	4000
Breaking capacity AC23A 400V			A	3200
Mechanical life			cycles	10000
<b>Mechanical features</b>				
Operating position		normal allowable	Vertical plan Any	
Fixing			Screw	
Terminals		type	M10 x 25	
Tightening torque for terminals				
		min	Nm	30
		max	Nm	37
		min	lbin	265
		max	lbin	327

Conductor section

IEC min	mm <sup>2</sup>	1X182
IEC max	mm <sup>2</sup>	2X185
AWG/kcmil min		1X400
AWG/kcmil max	kcmil	2X350

UL technical data

UL Standard	UL1008	
General purpose current rating	A	400
Operating voltage max	V	600
Horsepower/FLA current three phase motor		
	240V	HP/A 125/312
	480V	HP/A 250/302
	600V	HP/A 350/336
Short circuit rating	kA rms	100
Short circuit rating with fuse	Class/A	J/400
UL Terminal kit lugs	GLX502- GLX503	


Minimum enclosure dimensions at rated current

mm	mm	950 x 350 x 260
in	in	37.4 x 13.8 x 10.4


Ambient conditions

Operating temperature			
	min	°C	-25
	max	°C	+55
Storage temperature			
	min	°C	-40
	max	°C	+70
Max altitude		m	3000

Dimensions



Wiring diagrams



**Certifications and compliance**

Compliance

IEC/EN 60947-1

IEC/EN 60947-3

IEC/EN 60947-6-1

Certifications

cULus

**ETIM classification**

ETIM 8.0

EC000216 -  
 Switch  
 disconnecter