

Product datasheet

Specifications



integrated servo motor - 5.8 Nm -
3000 rpm - multiturn - with brake -
IP65

ILM1003P22F0000

EAN Code: 3606485294506

Main

Range of product	PacDrive 3
Product or component type	Servo motor integrated drive
Device short name	ILM

Complementary

[Us] rated supply voltage	250...700 V
Continuous stall current	3.6 A
Continuous stall torque	5.8 N.m
Peak stall torque	28.3 N.m
Nominal output power	1100 W
nominal torque	3.5 N.m
Nominal speed	3000 rpm
Maximum current Irms	21.2 A
[In] rated current	2.4 A
Shaft end	Untapped
Second shaft	Without second shaft end
Shaft diameter	19 mm
Shaft length	40 mm
key width	30 mm
Feedback type	Absolute multiturn SinCos Hiperface
Speed feedback resolution	128 periods
Holding brake	With
Holding torque	9 N.m holding brake
Mounting support	International standard flange
Motor flange size	100 mm
Torque constant	1.61 N.m/A at 120 °C
Back emf constant	103 V/krpm at 20 °C
Number of motor poles	8
Rotor inertia	3.92 kg.cm²
Stator resistance	2.6 Ohm at 20 °C for Ph/Ph 1.81 Ohm at 120 °C for Ph/N

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Stator inductance	15.6 mH at 20 °C for Ph/Ph 7.8 mH at 120 °C for Ph/N
Maximum radial force Fr	1050 N at 1000 rpm 830 N at 2000 rpm 730 N at 3000 rpm
Maximum axial force Fa	0.2 x Fr
type of cooling	Natural convection
Length	315 mm
Number of motor stacks	3
Centring collar diameter	95 mm
centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Net weight	8.9 kg

Environment

IP degree of protection	IP65
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.0 cm
Package 1 Width	20.0 cm
Package 1 Length	59.0 cm
Package 1 Weight	9.59 kg

Logistical informations

Country of origin	DE
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No