



FDFME3N311ZT

Integrated N-Channel PowerTrench® MOSFET and Schottky Diode 30 V, 1.8 A, 299 mΩ

Features

- Max $r_{DS(on)}$ = 299 mΩ at $V_{GS} = 4.5$ V, $I_D = 1.6$ A
- Max $r_{DS(on)}$ = 410 mΩ at $V_{GS} = 2.5$ V, $I_D = 1.3$ A
- Low profile: 0.55 mm maximum in the new package MicroFET 1.6x1.6 **Thin**
- Free from halogenated compounds and antimony oxides
- HBM ESD protection level > 1600 V (Note 3)
- RoHS Compliant



General Description

This device is designed specifically as a single package solution for a boost topology in cellular handset and other ultra-portable applications. It features a MOSFET with low input capacitance, total gate charge and on-state resistance. An independently connected schottky diode with low forward voltage and reverse leakage current to maximize boost efficiency.


The MicroFET 1.6x1.6 **Thin** package offers exceptional thermal performance for its physical size and is well suited to switching and linear mode applications.

Application

- Boost Functions




TOP



BOTTOM

MicroFET 1.6x1.6 Thin



MOSFET Maximum Ratings $T_A = 25$ °C unless otherwise noted

| Symbol | Parameter | Ratings | Units |
|----------------|--|-------------|-------|
| V_{DS} | Drain to Source Voltage | 30 | V |
| V_{GS} | Gate to Source Voltage | ±12 | V |
| I_D | Drain Current -Continuous $T_A = 25$ °C (Note 1a) | 1.8 | A |
| | -Pulsed | 4.5 | |
| P_D | Power Dissipation for Single Operation $T_A = 25$ °C (Note 1a) | 1.4 | W |
| | Power Dissipation for Single Operation $T_A = 25$ °C (Note 1b) | 0.6 | |
| V_{RRM} | Schottky Repetitive Peak Reverse Voltage | 28 | V |
| I_O | Schottky Average Forward Current | 1 | A |
| T_J, T_{STG} | Operating and Storage Junction Temperature Range (Note 4) | -55 to +150 | °C |

Thermal Characteristics

| | | | |
|-----------------|--|-----|------|
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Single Operation) (Note 1a) | 90 | °C/W |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Single Operation) (Note 1b) | 195 | |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Single Operation) (Note 1c) | 110 | |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient (Single Operation) (Note 1d) | 234 | |

Package Marking and Ordering Information

| Device Marking | Device | Package | Reel Size | Tape Width | Quantity |
|----------------|--------------|------------------------------|-----------|------------|------------|
| 1T | FDFME3N311ZT | MicroFET 1.6x1.6 Thin | 7" | 8mm | 5000 units |

Electrical Characteristics $T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted

| Symbol | Parameter | Test Conditions | Min | Typ | Max | Units |
|--------|-----------|-----------------|-----|-----|-----|-------|
|--------|-----------|-----------------|-----|-----|-----|-------|

Off Characteristics

| | | | | | | |
|--------------------------------------|---|---|----|----|----------|----------------------|
| BV_{DSS} | Drain to Source Breakdown Voltage | $I_D = 250\text{ }\mu\text{A}$, $V_{GS} = 0\text{ V}$ | 30 | | | V |
| $\frac{\Delta BV_{DSS}}{\Delta T_J}$ | Breakdown Voltage Temperature Coefficient | $I_D = 250\text{ }\mu\text{A}$, referenced to $25\text{ }^\circ\text{C}$ | | 25 | | mV/ $^\circ\text{C}$ |
| I_{DSS} | Zero Gate Voltage Drain Current | $V_{DS} = 24\text{ V}$, $V_{GS} = 0\text{ V}$ | | | 1 | μA |
| I_{GSS} | Gate to Source Leakage Current | $V_{GS} = \pm 12\text{ V}$, $V_{DS} = 0\text{ V}$ | | | ± 10 | μA |

On Characteristics

| | | | | | | |
|--|--|--|-----|-----|-----|----------------------|
| $V_{GS(th)}$ | Gate to Source Threshold Voltage | $V_{GS} = V_{DS}$, $I_D = 250\text{ }\mu\text{A}$ | 0.5 | 1 | 1.5 | V |
| $\frac{\Delta V_{GS(th)}}{\Delta T_J}$ | Gate to Source Threshold Voltage Temperature Coefficient | $I_D = 250\text{ }\mu\text{A}$, referenced to $25\text{ }^\circ\text{C}$ | | -3 | | mV/ $^\circ\text{C}$ |
| $r_{DS(on)}$ | Drain to Source On Resistance | $V_{GS} = 4.5\text{ V}$, $I_D = 1.6\text{ A}$ | | 235 | 299 | m Ω |
| | | $V_{GS} = 2.5\text{ V}$, $I_D = 1.3\text{ A}$ | | 296 | 410 | |
| | | $V_{GS} = 4.5\text{ V}$, $I_D = 1.6\text{ A}$, $T_J = 125\text{ }^\circ\text{C}$ | | 365 | 603 | |
| g_{FS} | Forward Transconductance | $V_{DS} = 5\text{ V}$, $I_D = 1.6\text{ A}$ | | 2.8 | | S |

Dynamic Characteristics

| | | | | | | |
|-----------|------------------------------|--|--|-----|----|----------|
| C_{iss} | Input Capacitance | $V_{DS} = 15\text{ V}$, $V_{GS} = 0\text{ V}$, $f = 1\text{ MHz}$ | | 55 | 75 | pF |
| C_{oss} | Output Capacitance | | | 15 | 20 | pF |
| C_{rss} | Reverse Transfer Capacitance | | | 7 | 10 | pF |
| R_g | Gate Resistance | | | 7.5 | | Ω |

Switching Characteristics

| | | | | | | |
|--------------|-------------------------------|--|--|-----|-----|----|
| $t_{d(on)}$ | Turn-On Delay Time | $V_{DD} = 15\text{ V}$, $I_D = 1.6\text{ A}$, $V_{GS} = 4.5\text{ V}$, $R_{GEN} = 6\text{ }\Omega$ | | 6 | 12 | ns |
| t_r | Rise Time | | | 8 | 16 | ns |
| $t_{d(off)}$ | Turn-Off Delay Time | | | 22 | 35 | ns |
| t_f | Fall Time | | | 1.4 | 10 | ns |
| Q_g | Total Gate Charge | | | 1 | 1.4 | nC |
| Q_{gs} | Gate to Source Gate Charge | $V_{GS} = 4.5\text{ V}$, $V_{DD} = 15\text{ V}$, $I_D = 1.6\text{ A}$ | | 0.2 | | nC |
| Q_{gd} | Gate to Drain "Miller" Charge | | | 0.3 | | nC |

Drain-Source Diode Characteristics

| | | | | | | |
|----------|---------------------------------------|---|--|-----|-----|----|
| V_{SD} | Source to Drain Diode Forward Voltage | $V_{GS} = 0\text{ V}$, $I_S = 0.9\text{ A}$ (Note 2) | | 0.9 | 1.2 | V |
| t_{rr} | Reverse Recovery Time | $I_F = 1.6\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$ | | 12 | 22 | ns |
| Q_{rr} | Reverse Recovery Charge | | | 3.1 | 10 | nC |

Schottky Diode Characteristics

| | | | | | | | |
|-------|-----------------|-----------------------|----------------------------------|--|------|------|---------------|
| I_R | Reverse Leakage | $V_R = 28\text{ V}$ | $T_J = 25\text{ }^\circ\text{C}$ | | 15 | 100 | μA |
| | | | $T_J = 85\text{ }^\circ\text{C}$ | | 0.46 | 4.7 | mA |
| V_F | Forward Voltage | $I_F = 1\text{ A}$ | $T_J = 25\text{ }^\circ\text{C}$ | | 0.47 | 0.57 | V |
| | | | $T_J = 85\text{ }^\circ\text{C}$ | | 0.45 | | |
| V_F | Forward Voltage | $I_F = 500\text{ mA}$ | $T_J = 25\text{ }^\circ\text{C}$ | | 0.38 | 0.48 | V |
| | | | $T_J = 85\text{ }^\circ\text{C}$ | | 0.33 | | |

Electrical Characteristics


Notes:

1. $R_{\theta JA}$ is determined with the device mounted on a 1 in² oz. copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta JA}$ is determined by the user's board design.

- (a) MOSFET $R_{\theta JA} = 90$ °C/W when mounted on a 1 in² pad of 2 oz copper, 1.5 " x 1.5 " x 0.062 " thick PCB.
- (b) MOSFET $R_{\theta JA} = 195$ °C/W when mounted on a minimum pad of 2 oz copper.
- (c) Schottky $R_{\theta JA} = 110$ °C/W when mounted on a 1 in² pad of 2 oz copper, 1.5 " x 1.5 " x 0.062" thick PCB.
- (d) Schottky $R_{\theta JA} = 234$ °C/W when mounted on a minimum pad of 2 oz copper.




a. 90 °C/W when mounted on a 1 in² pad of 2 oz copper.



b. 195 °C/W when mounted on a minimum pad of 2 oz copper.



c. 110 °C/W when mounted on a 1 in² pad of 2 oz copper.



d. 234 °C/W when mounted on a minimum pad of 2 oz copper.

- 2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.
- 3. The diode connected between the gate and source serves only as protection ESD. No gate overvoltage rating is implied.
- 4. Rating is applicable to MOSFET only.

Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 1. On Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Forward Bias Safe Operating Area




Figure 10. Gate Leakage Current vs Gate to Source Voltage




Figure 11. Schottky Diode Reverse Current




Figure 12. Schottky Diode Forward Voltage

Typical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted




Figure 13. Single Pulse Maximum Power Dissipation








Figure 14. Junction-to-Ambient Transient Thermal Response Curve

Dimensional Outline and Pad Layout





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

- | | | | |
|--------------------------|------------------------|---------------------------------------|--|
| AccuPower™ | F-PFS™ | Power-SPM™ | <p>SYSTEM GENERAL® The Power Franchise® the power franchise® TinyBoost™ TinyBuck™ TinyCalc™ TinyLogic® TINYOPTO™ TinyPower™ TinyPWM™ TinyWire™ TriFault Detect™ TRUECURRENT™* µSerDes™ SerDes® UHC® Ultra FRFET™ UniFET™ VCX™ VisualMax™ XST™</p> |
| Auto-SPM™ | FRFET® | PowerTrench® | |
| Build it Now™ | Global Power Resource™ | PowerXST™ | |
| CorePLUS™ | Green FPS™ | Programmable Active Droop™ | |
| CorePOWER™ | Green FPS™ e-Series™ | QFET® | |
| CROSSVOLT™ | Gmax™ | QS™ | |
| CTL™ | GTO™ | Quiet Series™ | |
| Current Transfer Logic™ | IntelliMAX™ | RapidConfigure™ | |
| DEUXPEED® | ISOPLANAR™ | Saving our world, 1mW/W/kW at a time™ | |
| Dual Cool™ | MegaBuck™ | SignalWise™ | |
| EcoSPARK® | MICROCOUPLER™ | SmartMax™ | |
| EfficientMax™ | MicroFET™ | SMART START™ | |
| ESBC™ | MicroPak™ | SPM® | |
| Fairchild® | MillerDrive™ | STEALTH™ | |
| Fairchild Semiconductor® | MotionMax™ | SuperFET™ | |
| FACT Quiet Series™ | Motion-SPM™ | SuperSOT™_3 | |
| FACT® | OptiHiT™ | SuperSOT™_6 | |
| FAST® | OPTOLOGIC® | SuperSOT™_8 | |
| FastvCore™ | OPTOPLANAR® | SupreMOS™ | |
| FETBench™ | PDP SPM™ | SyncFET™ | |
| FlashWriter® * | | Sync-Lock™ | |
| FPS™ | | | |

*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

| Datasheet Identification | Product Status | Definition |
|--------------------------|-----------------------|---|
| Advance Information | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice. |
| Preliminary | First Production | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design. |
| Obsolete | Not In Production | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only. |

Rev. 148