




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **3**
Centerline (Pitch): **5 mm [.197 in]**
Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Block Type	Special Plug
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1
Wire Entry Angle	Side

Electrical Characteristics

Current Rating (Max)	12 A
Voltage Rating	300 VAC

Body Features

Interlock	Without
-----------	---------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	12 A



Mechanical Attachment

Mating Angle	90°(Bottom)/ 180° (Side)
Screwless Terminal Block	Yes
Mounting Angle	Right Angle, Vertical
Screw Size	M3
Screw Plating Material	Nickel
Screw Material	Brass
Screw Flange	Without

Housing Features

Housing Color	Green
Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Wire Size	.05 – 2 mm²
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Marking Color	Black
---------------	-------

Packaging Features

Packaging Quantity	200
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (.54% in Component Part)







Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1546931-3 3P UNSHROUD 5.0 HDR,HIGH TEMP	 TE Part # 282827-3 TERMI-BLOK HEADER,ASSY90 3P.	 TE Part # 282832-3 TERMI-BLOK PIN HEAD 180 3P. 5	 TE Part # 1546018-3 3 POS TERMI-BLOK PLUG 90 & 180
 TE Part # 2-1546931-9 5P UNSHROUD 5.0 HDR,HIGH TEMP	 TE Part # 3-282832-3 TERMI-BLOK PIN HEADER 5MM STAC	 TE Part # 1986866-3 3P HDR, 5MM, 90DEG, SIDE STK	

Customers Also Bought



TE Part #5747871-2
09 PLUG SP/FMS STD



TE Part #7-338069-4
MICRO-MATCH SMD FTE




TE Part #5145323-1
SMT CARD CONN LOW PROFILE
8POS




TE Part #63499-1
MAG-MATE 250 F TAB 30-27 TPBR
8POS




TE Part #2-1445053-2
MICRO MNL HDR ASSY S/ROW LF



TE Part #640388-2
02P MTA156 HDR ASSY RN STR F/L



TE Part #63982-1
187 FASTON TAB TPBR



TE Part #61018-1
.058 PCB PIN PTPPHBZ



TE Part #1986525-2
Hi Rise Header, 5.0mm, 2 posn



TE Part #1986525-4
Hi Rise Header, 5.0mm, 4 posn

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_282830-3_L2.3d_igs.zip

English

Customer View Model

ENG_CVM_282830-3_L2.3d_stp.zip

English

Customer View Model

ENG_CVM_282830-3_L2.2d_dxf.zip

English

3D PDF

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_282830-3_H.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_282830-3_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_282830-3_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English