

Features

Abrasive cones are ideal for removing burrs, smoothing edges, grinding welds and removing machining marks in hard-to-reach areas such as corners, holes or moulds.

Its design ensures continuous release of new abrasive grains as the outer layer wears, allowing for precise control of the grinding process.

Available in various grits.

For use with handheld machines (straight grinders or flexible shaft grinders) after mounting on a suitable mandrel.

Applications:

- Deburring
- Cleaning
- Finishing operations

RS PRO Sanding Drums

**RS Stock No.: 0768306, 0768307, 0768309,
0768311, 0768313, 0768315**



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The Abrasive Cones are designed for grinding and finishing internal contours and deep holes. The tool is suitable for stainless steel, steel, aluminium alloys, bronze, and brass. This abrasive tool is designed for repeated use and must be used with the corresponding mandrel and powered by a straight grinder or a drill.

General Specifications

Dimensions (Diameter D x Length L x Hole H)	10 mm x 50 mm x 8 mm
Grain Type	Aluminium Oxide (A/O)
Material (Backing/Coating)	Heavy Cotton Cloth / Close coat

Mechanical Specifications

Available Grits	P60, P80, P100, P120, P150, P180
Recommended Mandrel	0768258
Recommended Speed	15,000 min ⁻¹
Maximum Speed	23,000 min ⁻¹

Grits vs RS Pro Codes

Grits	RS Pro Codes
P60	0768306
P80	0768307
P100	0768309
P120	0768311
P150	0768313
P180	0768315