



EN ISO 20344:2011



SCOUT
TONALE
30329-06L

S3 *CI HRO HI SRC

Size: 36-50
Weight: 735 gr.

Fit: 11

Working Environment:
Building, Wood-metal carpentry,
Farming and Gardening,
Mountains



FEATURES

UPPER

Greased Nubuk Dakar Leather
Hydro 1,8-2,0 mm
Reflex insert

LINING

3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Qrs01

TOE CAP

Alu SXT 2.0 Toe cap

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU-RUBBER VIBRAM-FIRE&ICE

PU foam insole, light and comfortable. Modular overtote to protect uppers. VIBRAM rubber tread with Fire & ICE mix for high performance in all temperatures. Self-cleaning design with special SRC grip.

TECHNOLOGIES

Removable Insole



Anatomical breathable insole. Resistant fabric with recycled open-cell foam that absorbs shocks and reduces fatigue. Eliminates sweat with its high ability to evaporate it. Continuous comfort for months and months of use



Protection elements



RESISTANT
TO 3.0 mm.
NAILS



Toecap "Alu Sxt 2.0" with differentiated thicknesses, resistant to 200J. Non metal perforation resistant Insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic **HC** control
technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other

DUALMICRO
DUALMICRO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



SRC (SRA+SRB)



	FLAT ≥0.32 HEEL (CONTACT ANGLE 1°) ≥0.28	0.53
SRA CERAMIC + DETERGENT SOLUTION		0.49
	FLAT ≥0.18 HEEL (CONTACT ANGLE 1°) ≥0.13	0.23
SRB STEEL + GLYCEROL		0.18

EN ISO 20344:2011