

- Highest power density in SIP-8 metal package (optional plastic package)
- Ultra wide 4:1 input voltage range
- Temperature range  $-40^{\circ}$  to  $+85^{\circ}\text{C}$
- High efficiency up to 89%
- Indefinite short-circuit protection
- I/O isolation 1600 VDC
- Remote On/Off control
- Fully RoHS compliant
- 3-year product warranty



The TMR 9WI series is a new family of isolated 9W DC/DC converter modules with regulated output, featuring ultra wide 4:1 input voltage ranges. The product comes in a ultra-compact SIP-8 metal package with a small footprint occupying only 2.0 cm<sup>2</sup> (0.3 square inch) of board space.

An excellent efficiency allows  $-40^{\circ}$  to  $+60^{\circ}\text{C}$  operation temperatures without derating. Further features include remote On/Off control and continuous short circuit protection. The very compact dimensions of these converters make them an ideal solution for many space critical applications in communication equipment, instrumentation and industrial electronics.

### Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I <sub>max</sub>	Vnom	I <sub>max</sub>	
TMR 9-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2'000 mA			82 %
TMR 9-2411WI		5 VDC	1'600 mA			85 %
TMR 9-2419WI		9 VDC	1'000 mA			88 %
TMR 9-2412WI		12 VDC	750 mA			88 %
TMR 9-2413WI		15 VDC	600 mA			89 %
TMR 9-2415WI		24 VDC	375 mA			89 %
TMR 9-2421WI		+5 VDC	800 mA	-5 VDC	800 mA	86 %
TMR 9-2422WI		+12 VDC	375 mA	-12 VDC	375 mA	88 %
TMR 9-2423WI		+15 VDC	300 mA	-15 VDC	300 mA	88 %
TMR 9-4810WI		18 - 75 VDC (48 VDC nom.)	3.3 VDC	2'000 mA		
TMR 9-4811WI	5 VDC		1'600 mA			85 %
TMR 9-4819WI	9 VDC		1'000 mA			89 %
TMR 9-4812WI	12 VDC		750 mA			89 %
TMR 9-4813WI	15 VDC		600 mA			89 %
TMR 9-4815WI	24 VDC		375 mA			89 %
TMR 9-4821WI	+5 VDC		800 mA	-5 VDC	800 mA	85 %
TMR 9-4822WI	+12 VDC		375 mA	-12 VDC	375 mA	88 %
TMR 9-4823WI	+15 VDC		300 mA	-15 VDC	300 mA	87 %

### Options

Suffix -P	- models with plastic case
-----------	----------------------------

## Input Specifications

Input Current	- at no load	24 Vin models: <b>7 mA typ.</b> 48 Vin models: <b>3 mA typ.</b>
Surge Voltage		24 Vin models: <b>50 VDC max.</b> (1 s max.) 48 Vin models: <b>100 VDC max.</b> (1 s max.)
Recommended Input Fuse		24 Vin models: <b>3150 mA</b> (slow blow) 48 Vin models: <b>1250 mA</b> (slow blow)
Input Filter		<b>Internal Capacitor</b>

## Output Specifications

Voltage Set Accuracy		<b>±1% max.</b>
Regulation	- Input Variation (Vmin - Vmax)	single output models: <b>0.2% max.</b> dual output models: <b>0.2% max.</b>
	- Load Variation (0 - 100%)	single output models: <b>1% max.</b> dual output models: <b>1% max.</b> (Output 1) <b>1% max.</b> (Output 2)
	- Cross Regulation (25% / 100% asym. load)	dual output models: <b>5% max.</b>
Ripple and Noise (20 MHz Bandwidth)	- single output	3.3 Vout models: <b>50 mVp-p typ.</b> (with 1 µF X7R) 5 Vout models: <b>50 mVp-p typ.</b> (with 1 µF X7R) 9 Vout models: <b>50 mVp-p typ.</b> (with 1 µF X7R) 12 Vout models: <b>75 mVp-p typ.</b> (with 1 µF X7R) 15 Vout models: <b>75 mVp-p typ.</b> (with 1 µF X7R) 24 Vout models: <b>75 mVp-p typ.</b> (with 1 µF X7R)
	- dual output	5 / -5 Vout models: <b>50 / 50 mVp-p typ.</b> (with 1 µF X7R) 12 / -12 Vout models: <b>75 / 75 mVp-p typ.</b> (with 1 µF X7R) 15 / -15 Vout models: <b>75 / 75 mVp-p typ.</b> (with 1 µF X7R)
Capacitive Load	- single output	3.3 Vout models: <b>2'600 µF max.</b> 5 Vout models: <b>1'300 µF max.</b> 9 Vout models: <b>800 µF max.</b> 12 Vout models: <b>560 µF max.</b> 15 Vout models: <b>560 µF max.</b> 24 Vout models: <b>200 µF max.</b>
	- dual output	5 / -5 Vout models: <b>800 / 800 µF max.</b> 12 / -12 Vout models: <b>390 / 390 µF max.</b> 15 / -15 Vout models: <b>200 / 200 µF max.</b>
Minimum Load		<b>Not required</b>
Temperature Coefficient		<b>±0.02 %/K max.</b>
Start-up Time		<b>50 ms typ.</b>
Short Circuit Protection		<b>Continuous, Automatic recovery</b>
Output Current Limitation		<b>180% typ. of Iout max.</b>
Transient Response	- Response Time	<b>250 µs typ.</b> (25% Load Step)

## Safety Specifications

Safety Standards	- IT / Multimedia Equipment	IEC 60950-1 EN 60950-1 UL 60950-1
	- Certification Documents	<a href="http://www.tracopower.com/overview/tmr9wi">www.tracopower.com/overview/tmr9wi</a>
Pollution Degree		<b>PD 2</b>

## EMC Specifications

EMC Emissions	- Conducted Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- External Filter Proposal	<a href="http://www.tracopower.com/overview/tmr9wi">www.tracopower.com/overview/tmr9wi</a>

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

EMC Immunity	- Electrostatic Discharge	Air: EN 61000-4-2, $\pm 8$ kV, perf. criteria A
	- RF Electromagnetic Field	Contact: EN 61000-4-2, $\pm 6$ kV, perf. criteria A
	- EFT (Burst)	EN 61000-4-3, 20 V/m, perf. criteria A
	- Surge	EN 61000-4-4, $\pm 2$ kV, perf. criteria A
		EN 61000-4-5, $\pm 2$ kV, perf. criteria A
		Ext. Input Component: 24 Vin models: KY 220 $\mu$ F // SMDJ70A
		48 Vin models: KY 220 $\mu$ F // SMDJ120A
	- Conducted RF Disturbances	EN 61000-4-6, 10 Vrms, perf. criteria A
	- PF Magnetic Field	EN 61000-4-8, 100 A/m, perf. criteria A

## General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
Power Derating	- High Temperature	see application note <a href="http://www.tracopower.com/overview/tmr9wi">www.tracopower.com/overview/tmr9wi</a>
	- Low Input Voltage	see application note <a href="http://www.tracopower.com/overview/tmr9wi">www.tracopower.com/overview/tmr9wi</a>
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote	On: 0 to 0.5 VDC or open circuit Off: 3 to 12 VDC Refers to 'Remote' and '-Vin' Pin
	- Off Idle Input Current	2.5 mA max.
Altitude During Operation		2'000 m max.
Switching Frequency		400 kHz typ. (PWM) (single output models) 500 kHz typ. (PWM) (dual output models)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'600 VDC
	- Input to Case or PE, 60 s	1'000 VDC
	- Output to Case or PE, 60 s	1'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MOhm min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	50 pF max.
Reliability	- Calculated MTBF	2'940'000 h (for standard version) 2'640'000 h (for option -P) (MIL-HDBK-217F, ground benign)
Environment	- Vibration	MIL-STD-810F
	- Thermal Shock	MIL-STD-810F
Housing Material		Copper (for standard version) non-conductive plastic (for option -P)
Potting Material		Silicone (UL94 V-0 rated)
Connection Type		THD (Through-Hole Device)
Weight		5.9 g (for standard version)
		4.8 g (for option -P)
Environmental Compliance	- Reach	<a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a>
	- RoHS	<a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a>


## Supporting Documents

Overview Link (for additional Documents)	<a href="http://www.tracopower.com/overview/tmr9wi">www.tracopower.com/overview/tmr9wi</a>
--	--

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

### Outline Dimensions

#### Metal package (standard)




Dimensions in mm (inch)  
 Tolerances:  $\pm 0.5$  ( $\pm 0.02$ )  
 Pin pitch Tolerance  $\pm 0.25$  ( $\pm 0.01$ )

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9	Case	Case
10	Stand Off	Stand Off
11	Stand Off	Stand Off
12	Case	Case

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

### Plastic package (option)



Dimensions in mm (inch)  
 Tolerances:  $\pm 0.5$  ( $\pm 0.02$ )  
 Pin pitch Tolerance  $\pm 0.25$  ( $\pm 0.01$ )

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout