



Type Number..... 4274
Designation IEC..... LR 54
System..... Manganese Dioxide/
 Zinc/KOH-Electrolyte

Nominal Voltage..... 1,5V
Typical Capacity C..... 50 mAh
 Load 13 kOhm, at 20°C down to 1.2 V

Weight (approx.)..... 1,18 g
Volume..... 0,28 ccm
Coding..... Date of Manufacturing
 Month/Year

Temperature Ranges min max.
 Storage..... -10°C 65°C
 Discharge..... -10°C 65°C

Dimensions min max.
 Diameter (Ø)..... 11,25 11,6
 Height (A/B)..... 2,75 3,05

Segment..... Electronic

Main Applications..... Watch
 Photo
 Electronic

Self discharge (at 20°C) ≤3% / year

Discharge Type	Load	End Voltage:	
		1.2V	0.9V
Continuous	13000 Ω	Time: 465h	650h
24h/d, 7d/w		Capacity [mAh]: 50	63
Current [µA]	115	Energy [MWh]: 68	81

All Data contained herein is for single cells
 For battery applications, performance data may vary from single cell data, depending on specific battery configuration